


# Actuator

704.115.0



<https://eao.com/p/704.115.0>

Your product:

---



## 704.115.0 Actuator

### FRONT

<b>Front dimension:</b>	Ø 29 mm
<b>Front bezel colour:</b>	Nature
<b>Front bezel material:</b>	Aluminium

### MOUNTING

<b>Design:</b>	raised
----------------	--------

### ELECTRICAL CHARACTERISTICS

<b>Standards:</b>	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

### MECHANICAL CHARACTERISTIC

<b>Switching angle:</b>	42° left / 42° right
<b>Switching positions:</b>	3 positions
<b>Mechanical lifetime:</b>	≤50 000 cycles of operation
<b>Weight:</b>	0.07 kg
<b>Switching action:</b>	Momentary - Rest (a) - Momentary

### AMBIENT CONDITION

<b>IP Protection:</b>	IP65 front side
<b>Storage temperature:</b>	- 40 °C ... + 85 °C
<b>Operating temperature:</b>	- 40 °C ... + 55 °C

**OTHER**

**max. number of switching elements:**

3


**Short Description:**

Actuator, Ø 29 mm, Nature, Aluminium, Momentary - Rest (a) - Momentary

**Hints:**

The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on

**Mounting cut-outs:**



A = Screw terminal

B = Push-in terminal (PIT)


C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm


**Wiring diagrams:**



**Switching positions:**



**Dimension drawings:**



A = Screw terminal