



NOTES:

1. MATERIAL:
 - 1.1 HOUSING: HALOGEN FREE PLASTIC, HIGH TEMP.,
UL94V-0.
 - 1.2 CONTACT: COPPER ALLOY
 - 1.3 FITTING NAIL: COPPER ALLOY
2. FINISH:
 - 2.1 CONTACT:
50~100u" NICKEL UNDERPLATING OVERALL.
100u" MIN. MATT TIN ON CONTACT AND SOLDER
 - 2.2 CONTACT:
50~100u" NICKEL UNDERPLATING OVERALL.
GOLD FLASH ON CONTACT AND SOLDER
 - 2.3 FITTING NAIL: 50~100u" NICKEL UNDERPLATING OVERALL.
100u" MIN. MATT TIN
3. REFLOW SOLDER CAPABLE TO 260°C PER PRODUCTION SPEC.



BLACK	24.2	25.4	23.8	22.8	21.0	15P	7-2381626-5	5-2381626-5
	22.7	23.9	22.3	21.3	19.5	14P	7-2381626-4	5-2381626-4
	21.2	22.4	20.8	19.8	18.0	13P	7-2381626-3	5-2381626-3
	19.7	20.9	19.3	18.3	16.5	12P	7-2381626-2	5-2381626-2
	18.2	19.4	17.8	16.8	15.0	11P	7-2381626-1	5-2381626-1
	16.7	17.9	16.3	15.3	13.5	10P	7-2381626-0	5-2381626-0
	15.2	16.4	14.8	13.8	12.0	9P	6-2381626-9	4-2381626-9
	13.7	14.9	13.3	12.3	10.5	8P	6-2381626-8	4-2381626-8
	12.2	13.4	11.8	10.8	9.0	7P	6-2381626-7	4-2381626-7
	10.7	11.9	10.3	9.3	7.5	6P	6-2381626-6	4-2381626-6
	9.2	10.4	8.8	7.8	6.0	5P	6-2381626-5	4-2381626-5
	7.7	8.9	7.3	6.3	4.5	4P	6-2381626-4	4-2381626-4
6.2	7.4	5.8	4.8	3.0	3P	6-2381626-3	4-2381626-3	
4.7	5.9	4.3	3.3	1.5	2P	6-2381626-2	4-2381626-2	
NATURAL	24.2	25.4	23.8	22.8	21.0	15P	3-2381626-5	1-2381626-5
	22.7	23.9	22.3	21.3	19.5	14P	3-2381626-4	1-2381626-4
	21.2	22.4	20.8	19.8	18.0	13P	3-2381626-3	1-2381626-3
	19.7	20.9	19.3	18.3	16.5	12P	3-2381626-2	1-2381626-2
	18.2	19.4	17.8	16.8	15.0	11P	3-2381626-1	1-2381626-1
	16.7	17.9	16.3	15.3	13.5	10P	3-2381626-0	1-2381626-0
	15.2	16.4	14.8	13.8	12.0	9P	2-2381626-9	2381626-9
	13.7	14.9	13.3	12.3	10.5	8P	2-2381626-8	2381626-8
	12.2	13.4	11.8	10.8	9.0	7P	2-2381626-7	2381626-7
	10.7	11.9	10.3	9.3	7.5	6P	2-2381626-6	2381626-6
	9.2	10.4	8.8	7.8	6.0	5P	2-2381626-5	2381626-5
	7.7	8.9	7.3	6.3	4.5	4P	2-2381626-4	2381626-4
6.2	7.4	5.8	4.8	3.0	3P	2-2381626-3	2381626-3	
4.7	5.9	4.3	3.3	1.5	2P	2-2381626-2	2381626-2	
COLOR	DIM E	DIM D	DIM C	DIM B	DIM A	POS	GOLD FLASH	MATT TIN
							PLATING SPEC	
							PART NUMBER	

1470-19 (1/15)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A

A



NOTES:

- 1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE. ±0.20mm
- 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
- 3. ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
- 4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
- 5. THICKNESS: 0.40 ± 0.05 mm.
- 6. PACKING LENGTH PER 13" REEL : 12.0 METERS.
- 7. COMPONENT LOAD PER 13" REEL : 900 PCS.

POS.NO	A	B	C	D	E
2	4.0	6.3	7.5	16	16.4
3	5.5	7.8			
4	7.0	9.3	11.5	24	24.4
5	8.5	10.8			
6	10.0	12.3			
7	11.5	13.8			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTE

FINISH
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.35
2 PLC ± 0.25
3 PLC ± 0.15
4 PLC ± - ± 2°
ANGLES

DWN
Jone Ji
CHK
Wenke He
APVD
Wenke He
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT

22OCT2020
-
-
-
-
-

TE Connectivity Ltd.

NAME
1.5P WTB R/A TYPE WITH LATCH
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2381626

RESTRICTED TO
-


CUSTOMER DRAWING

SCALE
N/A


SHEET
2 of 4

REV
A

1470-19 (1/15)



1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE. $\pm 0.20\text{mm}$
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
3. ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
5. THICKNESS: $0.40 \pm 0.05 \text{ mm}$.
6. PACKING LENGTH PER 13" REEL : 12.0 METERS.
7. COMPONENT LOAD PER 13" REEL : 900 PCS.



POS.NO.	A	B	C	D	E
8	13.0	15.3	14.2	32	32.4
9	14.5	16.8			
10	16.0	18.3			
11	17.5	19.8	20.2	44	44.4
12	19.0	21.3			
13	20.5	22.8			
14	22.0	24.3			
15	23.5	25.8			

DWN	22OCT2020
Jone Ji	
CHK	-
Wenke He	

STE

0 PLC	± 0.5
1 PLC	± 0.35
2 PLC	± 0.25
3 PLC	± 0.15
4 PLC	$\pm -$
ANGLES	$\pm 2^\circ$

SEE NOTE

1

CHK	-
-----	---

Wenke He
PRODUCT SPEC

—

APPLICATION SPEC

[illegible]

WEIGHT

CUSTOMER DRAWING

NAME

1.5P WTB R/A TYPE
WITH LATCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A.3 00779 C-2381626

RESTRICTED TO

SCALE	N/A	SHEET	3 OF 4	REV	A
-------	-----	-------	--------	-----	---

