







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		N1	REVISED PER ECO-11-005030	11MAR11	RK	HMR



1. ACCEPTS COAX CABLE WITH .095-.110 O.D. JACKETS AND .055-.065 DIELECTRIC O.D.
EXAMPLE: RG-174 AND RG-316
2. TIN PLATE PER ASTM-B-545.
3. INSTRUCTION SHEET NO.: 408-2472-2.
4. ON STRIP
5. ON STRIP, LEGS MUST BE BENT MANUALLY AFTER CRIMPING.
6. LOOSE PIECE PARTS WITH PREFORMED LEGS.
7. BRASS PER ASTM-B-36.
8. TIN-LEAD PLATE PER ASTM-B-545.




VIEW C



VIEW D

SECTION A-A

SECTION B-B



PCB LAYOUT



AS APPLIED BY APPLICATOR

AS APPLIED BY APPLICATOR

VIEW E

VIEW F

2	D	6	9-226176-2
2	C&F	5	9-226176-1
2	C&E	4	9-226176-0
8	D	6	226176-4
8	C&F	5	226176-3
8	C&E	4	226176-2
FINISH	VIEW	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. OBRINE	30JUN99	 TE Connectivity			
		CHK M. OBRINE	30JUN99				
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. CABRILLO	30JUN99	NAME BRAID-PIC P.C. BOARD GROUND TERMINAL SINGLE CRIMP-SINGLE CONTACT			
	0 PLC ± -	PRODUCT SPEC	—				
	1 PLC ± -	—	—				
	2 PLC ± -	—	—				
	3 PLC ± .008	APPLICATION SPEC	—				
	4 PLC ± -	—	—				
	ANGLES ± -	—	—				
MATERIAL	FINISH	WEIGHT	.007 OZ	SIZE A2	CAGE CODE 00779	DRAWING NO C-226176	RESTRICTED TO —
SEE NOTE 7	SEE TABLE	CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1	REV N1