

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1

PART NUMBER

BXQC4L354

REVISION HISTORY

REV	DOCUMENT	DESCRIPTION	CHG'D BY	DATE	APPROVED
B	0113921	REDRAWN WITH CHANGE	RKA	2014-09-11	M. MANTUA
C	0120854	REVISED PER ECO	RGA	2015-05-21	M. MANTUA

EXTERNAL GROUND SCREW

ONL AC

DETAIL B

39.62
[1.56]

17.53
[.69]

41.15
[1.62]

46.48
[1.83]

85.73
[3.38]

5.08
[.20]

2X Ø5.16
[.203]
MTG. HOLES

38.10
[1.50]

50.80
[2.00]

22.23
[.875]
MIN

2X 5/16 - 18 UNC - 2B
TAPPED FROM REAR

SEE DETAIL B

COVER LOCKING CLAMP

CAUTION
USE ONLY NON-SPARKING
ACTUATORS

(138.18)
[5.44]

96.77
[3.81]

DOUBLE POLE

MOMENTARY

4

3

2

1

8

7

6

5

10 AMP CONT.

A.C VOLTAGE	AMPS		POWER FACTOR
	MAKE	BREAK	
120	30	3	.35
240	15	1.5	.35
480	7.5	.75	.35
600	6	.6	.35

	MAKE & BREAK	
D.C VOLTAGE	INDUCTIVE	RESISTIVE
120	0.25	0.80
240	0.15	0.40

OPERATING POINT GIVEN
IN RELATION TO TOP MOUNTING HOLES

CHARACTERISTICS	BXC PLUNGER
PRETRAVEL (MAX)	1.79 / .070
DIFFERENTIAL TRAVEL (MAX)	0.51 / .020
OVERTRAVEL (MIN)	4.83 / .190
OPERATING FORCE (MAX)	17.86 N / 4 LBS
OPERATING POINT	58.55 ±.76 / 2.305±.030
FULL OVERTRAVEL FORCE (MAX)	31.25 N / 7 LBS

PRE-TRAVEL

OVER TRAVEL

DIFFERENTIAL TRAVEL

FULL TRAVEL

OPERATING POINT

RELEASE POINT

CAUTION

NOTES:

1 - CONSTRUCTED IN ACCORDANCE WITH EN-50014 / EN - 50018 GROUP II C

2 - VOLUME 27 CU.IN(442 CU.CM) APPROX. TOP AND SIDE PLUNGER

3 - EXPLOSION PROOF - UNDER WRITERS LAB INC. LISTED FOR HAZARDOUS LOCATIONS CLASS I, GROUPS B,C AND D; CLASS II GROUPS E,F, AND G.

4 - SIRA CERTIFIED PRODUCT. NO MODIFICATIONS PERMITTED WITHOUT REFERENCE TO SIRA.

5 - CONFORMS TO EExd IIC TG
SIRA 00ATEXI037X
CAT 112 GD.

6 - FURNISHED UNASSEMBLED IN A SEPARATE PLASTIC BAG.

7 - ENCLOSURE WIDTH 50.80±0.13/2.000±.005 FOR A LENGTH OF 5.08/.20 MIN

8 - APPROVED FOR RUSSIAN CUSTOM UNION CERTIFICATION PER
НАННО <<ЦБЭ>> РОСС RU.0001.11ГБ05

a. CONFORMS TO
IEx d IIC T6 Gb X
Ex tb IIIC T85°C Db

b. APPLICABLE HEALTH AND SAFETY STANDARDS
ГОСТ Р МЭК 60079-0-2011
ГОСТ IEC 60079-1-2011
ГОСТ Р МЭК 60079-31 2010

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1