

1

2


3

4

5

6

7





### △ Dimension


|       |                           |
|-------|---------------------------|
| DIM L | $(N-1) \times 7.50 + 5.7$ |
| DIM A | $(N-1) \times 7.50 + 5.0$ |
| DIM B | $(N-1) \times 7.50$       |

N=Number of poles

| POLES   | Tolerance  |
|---------|------------|
| 2p-6p   | $\pm 0.15$ |
| 7p-12p  | $\pm 0.20$ |
| 13p-16p | $\pm 0.30$ |



SECTION P-P



△

2P mark

| SIGN | DATE     | DESCRIPTION                                             | APPROVER |
|------|----------|---------------------------------------------------------|----------|
| △    | 11/21'09 | The normal grey No. changed from RAL7004/P to RAL7035/D | Kind     |
| △    | 03/03'10 | Add the glue on the top                                 | Wellch   |
| △    | 03/03'10 | The wire strip length is changed from 7~8mm to 8~9mm    | Wellch   |
| △    | 04/06'10 | Add the 2P mark                                         | RUNNER   |
| △    | 02/21'13 | add the safety certification icon or update the drawing | Da cheng |
| △    |          |                                                         |          |

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

### Material

- Item 1 Terminal body:Thermoplastic ( UL94V-0 )
- Item 2 Terminal body:Thermoplastic ( UL94V-0 )
- Item 3 Terminal lever:Thermoplastic ( UL94V-0 ) Orange(RAL2011/P)
- Item 4 Wire guard:Stainless Steel
- Item 5 Female contact: PhBz ( CuSn ) Tin plated

### △ Electrical

cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG): 12-26
- Stranded wire(AWG): 12-26
- △ Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension:

HW xx A0 x 0 xxxx G

△ RoHS compliant  
(Lead<4%)  
In copper Alloy

No. OF POLES  
02 2 POLES  
03 3 POLES  
...  
16 16 POLES

### △ Body Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- △ 8 Grey(RAL7035/D)
- C Green(RAL6018/U)

0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                                  |                        |                        |          |             |           |       |
|----------|--------------------------------------------------|------------------------|------------------------|----------|-------------|-----------|-------|
| TITLE    | HW 7.50 Series Contact on down side <W/o Flange> |                        |                        |          |             |           |       |
| PART NO. | HWxxA0x0xxxxG                                    |                        |                        | DWG NO.  | 8HW0501     |           |       |
| APPROVED | CHECKED                                          | DESIGNED               | DRAWN                  | CUST NO. |             |           |       |
|          |                                                  | Da cheng<br>2013.02.21 | Da cheng<br>2013.02.21 |          | UNIT: mm    | Tolerance |       |
|          |                                                  |                        |                        |          | SCALE: NONE | X.        | ±0.50 |
|          |                                                  |                        |                        |          |             | X.X       | ±0.30 |
|          |                                                  |                        |                        |          |             | X.XX      | ±0.10 |
|          |                                                  |                        |                        |          |             | X°        | ±1°   |

SHEET: 01/01

REV.: F

1

2

3

4

5

6

7