

The LEDs can also be optionally controlled via the PLC.

The technical drawing shows two views of the MZ-6000 machine:

- Front View (Left):** Shows the top profile with a total height of 184 mm. The base width is 42 ± 0.3 mm. Key features include a central handle assembly labeled with numbers 1 through 7, a mounting bracket at the bottom labeled 8, and a base diameter of Ø 9 ± 0.3 mm.
- Side View (Right):** Shows the side profile with a total height of 170 mm. It includes a top section with a width of 51 mm and a depth of 21 mm. A main body section has a width of 46 mm and a depth of 19.5 mm. The base has a width of 45 mm and a depth of 37.5 mm. A mounting hole is specified as M20 x 1.5.

Technical drawing of the LED-2000 lighting fixture, showing front, side, and top views with dimensions in millimeters (mm).

Front View (Top):

- Overall width: 190 mm
- Mounting hole diameter: $\varnothing 25.5$ mm
- Mounting hole spacing: 100 mm
- Mounting hole offset: 50 mm
- Mounting hole diameter: $\varnothing 40$ mm
- Mounting hole offset: 50 mm
- Overall height: 100 mm

Side View (Middle):

- Overall height: 115 mm
- Mounting hole diameter: $\varnothing 25.5$ mm
- Mounting hole spacing: 100 mm
- Mounting hole offset: 50 mm
- Mounting hole diameter: $\varnothing 40$ mm
- Mounting hole offset: 50 mm

Top View (Bottom):

- Overall width: 190 mm
- Overall height: 115 mm
- Mounting hole diameter: $\varnothing 25.5$ mm
- Mounting hole spacing: 100 mm
- Mounting hole offset: 50 mm
- Mounting hole diameter: $\varnothing 40$ mm
- Mounting hole offset: 50 mm

[illegible]

139