





SIGN	DATE	DESCRIPTION	APPROVER
△	04/25'11	Material is changed	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



SECTION A-A



P.C.B Layout

DimL=(N/2-1)×3.5+4.9
DimP=(N/2-1)×3.5
DimK=(N/2-1)×3.5

N=Number of poles

POLES	Dim. Tol	Dim.L	Dim.P
2x2p-2x6p		±0.15	±0.10
2x7p-2x12p		±0.25	±0.20
2x13p-2x18p		±0.35	±0.30
2x19p-2x24p		±0.40	±0.35

Material:

- Item ③ Terminal housing: PA66 (UL 94V-0)
- △ ● Item ④ Male contact pin: Brass, Tin plated

Electrical:

- Voltage rating: 150V
- Current rating: 7A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:

cULus



V X xx 1 1 x 0 xxxx G

NO of plose
04 2x2 CONTACTS
06 3x2 CONTACTS
...
48 24x2 CONTACTS

RoHS
Pb<40,000ppm
0 Black
3 Orange
5 Green
6 Blue
8 Grey
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VX 3.5mm Series Close type Vertical			
PART NO.	VXxx11x0xxxxG			DWG NO.	8VX0005
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2011.04.25	Chen Bo 2011.04.25		
SHEET: 01/01				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
					X.XX ±0.10
					X° ±1°