




Dimension

A	$N \times 5.08 + 1.0$
B	$(N-1) \times 5.08$

N=Number of poles

	TOL			
	2p-6p	7p-12p	13p-18p	19p-24p
A	±0.10	±0.15	±0.20	±0.30
B	±0.10	±0.15	±0.20	±0.30



PCB Layout

SIGN	DATE	DESCRIPTION	APPROVER
△	11/19/07	PCB Layout changed	Tony
△	05/30/11	Wire strip length is changed from 6-7mm to 5-6mm	Steven
△	05/30/11	Add "cULus" Safety Approval logo	Steven
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:	
● Item① Terminal side housing:	Thermoplastic (UL94V-0)
● Item② Terminal housing:	Thermoplastic (UL94V-0)
● Item③ Terminal cover:	Thermoplastic (UL94V-0)
● Item④ Spring clamp:	Stainless steel
● Item⑤ Contact pin of short:	Brass, Tin plated
● Item⑥ Contact pin of middle:	Brass, Tin plated
● Item⑦ Contact pin of long:	Brass, Tin plated

Electrical:	cULus
● Voltage rating:	300V
● Current rating:	10A
● Wire range:	
● Solid wire(AWG):	12-28
● Stranded wire(AWG):	12-28
△ ● Wire strip length:	5-6mm
● Withstanding Voltage:	1.6KV
● Operating temperature:	-40°C to +115°C
● Soldering temperature:	250°C±10°C/5 Sec
△ ● Safety Approval:	cULus
● Critical dimension:	▽

HR xx 3 0 x 1 xxxx G

No. OF POLES	G: Pb<4000ppm
03: 3x1 POLES	0000: "@" Logo (Standard)
06: 3x2 POLES	000A: "ANYTEK" Mark
69: 3x23 POLES	Any special item by customer request.
72: 3x24 POLES	please contact sales department.
COLOR	
0: BLACK	
5: GREEN (RAL 6018/T)	
6: BLUE	
8: GREY (RAL 7004/P)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HR 5.08mm Series (Solder pins staggered by half the pin spacing)						
PART NO.	HRxx30x1xxxxG			DWG NO.	8HR0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Steven	Tony		UNIT: mm		
		2011.05.30	2007.11.19		SCALE: NONE		
					SHEET: 01/01		
					REV.: D		
					X. ±0.50		
					X.X ±0.30		
					X.XX ±0.10		
					X° ±1°		