

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.01.12	Add cULus standard	Jacke
△	2013.08.10	change the dimension from 0.93 to 1.07	Chen Bo
△	2013.08.10	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item a Terminal body:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn),Tin plated

Electrical

● Voltage rating: 300VAC

● Current rating: 8A

● Withstanding Voltage: 1.6kv

● Operating temperature: -40°C to +115°C

△ ● Soldering temperature: 260°C±5°C/5 Sec

△ ● Safety Approval: cULus

● Critical dimension: ∇

V7 xx 1 1 x 0 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

... ..

24 24 CONTACTS

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

9 White(RAL1102)

C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

N = Number of poles

Dim A=(N-1)×3.5+2.8

Dim B=(N-1)×3.5

Dim C=(N-1)×3.5+3.7

Dim D=(N-1)×3.5

	Dim A	Dim B	Dim C	Dim D
2-5p	±0.10	±0.10	±0.10	±0.10
6-10p	±0.15	±0.15	±0.15	±0.15
11-15p	±0.20	±0.20	±0.20	±0.20
16-20p	±0.25	±0.25	±0.25	±0.25
21-24p	±0.30	±0.30	±0.30	±0.30

P.C.B. LAYOUT

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 3.5mm series Vertical				
PART NO.	V7xx11x0xxxxG				DWG NO.	8V70001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Chen Bo	Chen Bo			X. ±0.5
		08/10`13	08/08`13			X.X ±0.3
						X.XX ±0.1
				SHEET: 01/01	UNIT: mm	X° ±1°
					SCALE: NONE	
					REV.: D	