

## SUMMARY

### # Wires

Low voltage	4
Fluidic	1



*Image is for illustrative purpose only*

Series	2P
Termination type	Female solder
IP rating	50
AWG wire size	30.00 - 22.00
Cable Ø	0.00 - 0.00 mm
Status	active
Matching parts	<a href="#">CAB.P12.GLA.C72G</a>

### Download

[Request a quote](#)  
[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	CL*: Fixed receptacle, nut fixing
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	4.16 g

### Performance

Configuration	2P.P12 : 1 Fluidic with valve, 4 Low V.
Insulator	L: PEEK for solder contacts
Rated Current	9 Amps

### Specifications


Test voltage (kV rms) Contact-contact: 0.85  
Air clearance min.: 0.6 mm  
Creepage distance min.: 0.6 mm

### Others

Endurance (Shell): >1000 mating cycles  
Temp (min / max): -50°C / +150°C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## DRAWINGS



## RECOMMENDED BY LEMO

### Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.