



SIGN	DATE	DESCRIPTION	APPROVER
△	2010.10.23	Add UL standard	Jacke
△	2010.10.23	The material is changed from Brass to copper	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




Material

- ⚠ ● Item **a** Male contact pin: Copper, Tin plated.
● Item **b** Terminal (housing): PA66 30%GF(UL94V-0)

Electrical cULus / IEC

- Voltage rating: 300V/160V
- Current rating: 10A/13A
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 



RECOMMENDED PCB LAYOUT

Poles	2p	3p	4p	5p	6p	7p	8p	9p	10p	11p	12p	13p
Dim L	7.00	10.5	14.0	17.5	21.0	24.5	28.0	31.5	35.0	38.5	42.0	45.5
Dim B	3.50	7.00	10.5	14.0	17.5	21.0	24.5	28.0	31.5	35.0	38.5	42.0
TOL	±0.15					±0.20						±0.25
Poles	14p	15p	16p	17p	18p	19p	20p	21p	22p	23p	24p	
Dim L	49.0	52.5	56.0	59.5	63.0	66.5	70.0	73.5	77.0	80.5	84.0	
Dim B	45.5	49.0	52.5	56.0	59.5	63.0	66.5	70.0	73.5	77.0	80.5	
TOL	±0.25					±0.30						

PART NO.

EL xx 11 x 3 xxxx G

02	2 POLES	→
03	3 POLES	
...	...	
24	24 POLES	

➤ Pb < 40,000ppm
(RoHS)

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

000 0 @ Logo
000 A ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK					CUSTOMER COPY					
					ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD					
TITLE		EL 3.5mm Right angle open Dip TYPE Series								
PART NO.		ELxx11x3xxxx G			DWG NO.		8EL0106			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance			
			Jacke 2010.10.24	Jacke 2010.10.24			UNIT: mm		X. ±0.50	
							SCALE: NONE		X.X ±0.30	
					SHEET: 01/01		REV: C		X.XX ±0.10	
									X° ±1°	
5				6				7		