

REV. C

PLOT SCALE: .125/ DIMSCALE: .1000

TOLERANCES ARE:



ONE PLACE DECIMALS $\pm .1[2.54]$ THREE PLACE DECIMALS $\pm .005[.13]$
TWO PLACE DECIMALS $\pm .01[.25]$ FOUR PLACE DECIMALS $\pm .0020[.051]$

ANGLES
 $\pm 2^\circ$

TITLE:
.050 x .050 C.L.
HOT PLUGGABLE
TERMINAL STRIP


DWG NO:

HPT-115-XX-XX-D-RA
SHEET 1 OF 1



HPT-115-XX-XX-D-RA


- No. OF POS**
 - 15 (PER ROW)
- LEAD STYLE**
 - 01: THROUGH HOLE
- PLATING**
 - L: LIGHT SELECTIVE GOLD (USE T-1S15-03-L)
 - S: SELECTIVE GOLD (USE T-1S15-03-S)
 - LM: LIGHT SELECTIVE GOLD, MATTE TIN ON TAIL (USE T-1S15-03-L)
 - SM: SELECTIVE GOLD, MATTE TIN ON TAIL (USE T-1S15-03-S)
- ROW SPECIFICATION**
 - D: DOUBLE ROW (USE FTSH-50-D)
- TAIL SPECIFICATION**
 - RA: RIGHT ANGLE



PACKAGING VIEW

PT-1-24-01-09
TP-24

PARTS TO BE PACKAGED IN TUBE
AS SHOWN.



SCALE: .75x

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

TABLE 1

TABLE 1	
POSITION NUMBER	"A"
15, 16	.138 [3.51]
01, 08, 23, 30	.197 [5.00]
ALL OTHERS	.167 [4.24]

NOTES:

1. TERMINALS TO BE SHEARED TO MEET DIMENSION SPECIFICATION.
2. MINIMUM PUSHOUT FORCE: .5 LB.
3. PARTS TO BE PACKAGED IN TUBE AS SHOWN.

santec

810 PROGRESS BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: D. GRAHAM 2-25-95

HPT-115-XX-XX-D-RA
SHEET 1 OF 1

EXISPROD\ASSEMBLY\050\HPT15ASM