

		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	A REVISION RELEASE	6JUNE2022	SY	HL
	B	UPDATE HARD TRAY IN SHEETS	24NOV2022	MC	HL

1471-9 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TAPE & REEL	88 X 13.92 X 24(W*D*P)	30u"	53.5	8	28	58	37	40.15	56	40.61	98	7-2371899-7
HARD TRAY	330 X 235 X 19.3	30u"	45.0	8	44.5	91	70	73.15	89	73.61	164	7-2371899-4
HARD TRAY	330 X 235 X 19.3	30u"	86.5	8	44.5	91	70	73.15	89	73.61	164	5-2371899-8
HARD TRAY	330 X 235 X 19.3	30u"	53.5	8	28	58	37	40.15	56	40.61	98	5-2371899-7
SOFT TRAY	338 X 235 X 20.3	30u"	36.5	8	19.5	41	20	23.15	39	23.61	64	5-2371899-6
SOFT TRAY	TBD	30u"	22.5	8	12.5	27	6	9.15	25	9.61	36	5-2371899-5
HARD TRAY	330 X 235 X 19.3	30u"	10.0	8	44.5	91	70	73.15	89	73.61	164	5-2371899-4
HARD TRAY	330 X 235 X 19.3	30u"	10.0	8	28	58	37	40.15	56	40.61	98	5-2371899-3
SOFT TRAY	338 X 235 X 20.3	30u"	10.0	8	19.5	41	20	23.15	39	23.61	64	5-2371899-2
SOFT TRAY	TBD	30u"	10.0	8	12.5	27	6	9.15	25	9.61	36	5-2371899-1
HARD TRAY	330 X 235 X 19.3	15u"	86.5	8	44.5	91	70	73.15	89	73.61	164	4-2371899-8
HARD TRAY	330 X 235 X 19.3	15u"	53.5	8	28	58	37	40.15	56	40.61	98	4-2371899-7
SOFT TRAY	338 X 235 X 20.3	15u"	36.5	8	19.5	41	20	23.15	39	23.61	64	4-2371899-6
SOFT TRAY	TBD	15u"	22.5	8	12.5	27	6	9.15	25	9.61	36	4-2371899-5
HARD TRAY	330 X 235 X 19.3	15u"	10.0	8	44.5	91	70	73.15	89	73.61	164	4-2371899-4
HARD TRAY	330 X 235 X 19.3	15u"	10.0	8	28	58	37	40.15	56	40.61	98	4-2371899-3
SOFT TRAY	338 X 235 X 20.3	15u"	10.0	8	19.5	41	20	23.15	39	23.61	64	4-2371899-2
SOFT TRAY	TBD	15u"	10.0	8	12.5	27	6	9.15	25	9.61	36	4-2371899-1
HARD TRAY	330 X 235 X 19.3	G/F	86.5	8	44.5	91	70	73.15	89	73.61	164	3-2371899-8
HARD TRAY	330 X 235 X 19.3	G/F	53.5	8	28	58	37	40.15	56	40.61	98	3-2371899-7
SOFT TRAY	338 X 235 X 20.3	G/F	36.5	8	19.5	41	20	23.15	39	23.61	64	3-2371899-6
SOFT TRAY	TBD	G/F	22.5	8	12.5	27	6	9.15	25	9.61	36	3-2371899-5
HARD TRAY	330 X 235 X 19.3	G/F	10.0	8	44.5	91	70	73.15	89	73.61	164	3-2371899-4
HARD TRAY	330 X 235 X 19.3	G/F	10.0	8	28	58	37	40.15	56	40.61	98	3-2371899-3
SOFT TRAY	338 X 235 X 20.3	G/F	10.0	8	19.5	41	20	23.15	39	23.61	64	3-2371899-2
SOFT TRAY	TBD	G/F	10.0	8	12.5	27	6	9.15	25	9.61	36	3-2371899-1
HARD TRAY	330 X 235 X 19.3	30u"	NA		44.5	91	70	73.15	89	73.61	164	2-2371899-4
HARD TRAY	330 X 235 X 19.3	30u"	NA		28	58	37	40.15	56	40.61	98	2-2371899-3
SOFT TRAY	338 X 235 X 20.3	30u"	NA		19.5	41	20	23.15	39	23.61	64	2-2371899-2
SOFT TRAY	TBD	30u"	NA		12.5	27	6	9.15	25	9.61	36	2-2371899-1
HARD TRAY	330 X 235 X 19.3	15u"	NA		44.5	91	70	73.15	89	73.61	164	1-2371899-4
HARD TRAY	330 X 235 X 19.3	15u"	NA		28	58	37	40.15	56	40.61	98	1-2371899-3
SOFT TRAY	338 X 235 X 20.3	15u"	NA		19.5	41	20	23.15	39	23.61	64	1-2371899-2
SOFT TRAY	TBD	15u"	NA		12.5	27	6	9.15	25	9.61	36	1-2371899-1
HARD TRAY	330 X 235 X 19.3	G/F	NA		44.5	91	70	73.15	89	73.61	164	2371899-4
HARD TRAY	330 X 235 X 19.3	G/F	NA		28	58	37	40.15	56	40.61	98	2371899-3
SOFT TRAY	338 X 235 X 20.3	G/F	NA		19.5	41	20	23.15	39	23.61	64	2371899-2
SOFT TRAY	TBD	G/F	NA		12.5	27	6	9.15	25	9.61	36	2371899-1
TYPE	L * W * H (TRAY)	PRECIOUS PLATING THICKNESS (TOTAL)	W	V	J	D	N	C	B	A	POS.	PART NUMBER
PACKAGE			MYLAR SIZE (PAGE 4)									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL

-

-

DWN SANDERS, YAN 08APR2020

CHK MIKE, CHEN 08APR2020

APVD HOPE, LU 08APR2020

PRODUCT SPEC 108-160247

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, STD, ONE SIDE OPEN

SIZE A2

CAGE CODE 00779

DRAWING NO C-2371899

RESTRICTED TO -



SCALE 6:1

SHEET 2 OF 6


REV B

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



1471-9 (3/13)




D


C

B

A



HARD TRAY: FOR 164POS
SCALE 1:2



HARD TRAY: FOR 98POS
SCALE 1:2

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.3
2 PLC	±0.20
3 PLC	±0.050
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL

-

-

DWN 08APR2020
SANDERS, YAN

CHK 08APR2020
MIKE, CHEN

APVD 08APR2020
HOPE, LU

PRODUCT SPEC
108-160247

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
GEN5, STD, ONE SIDE OPEN

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2371899

-


-

SCALE 4:1


SHEET 5 OF 6

REV B

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SOFT TRAY: FOR 64POS
SCALE 1:2



TAPE & REEL: FOR 7-2371899-7 (98POS)
SCALE 1:2