




		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	A REVISION RELEASE	7JUNE2022	SY	HL
	B	UPDATE HARD TRAY IN SHEET 5	24NOV2022	MC	HL



- 



SECTION X - X

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14DEC2020 SANDERS, YAN CHK 14DEC2020 MIKE, CHEN APVD 14DEC2020 HOPE, LU		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.050 4 PLC ±. ANGLES ±.		NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB AND CENTER POST	
MATERIAL -  - 		PRODUCT SPEC 108-160247 APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C-2384214 RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 6:1 SHEET 1 of 6 REV B	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

30 u"	45.0	8	44.5	70	72.45	89	71.65	164	7-2384214-4
30 u"	86.5	8	44.5	70	72.45	89	71.65	164	5-2384214-8
30 u"	53.5	8	28	37	39.45	56	38.65	98	5-2384214-7
30 u"	36.5	8	19.5	20	22.45	39	21.65	64	5-2384214-6
30 u"	22.5	8	12.5	6	8.45	25	7.65	36	5-2384214-5
30 u"	10.0	8	44.5	70	72.45	89	71.65	164	5-2384214-4
30 u"	10.0	8	28	37	39.45	56	38.65	98	5-2384214-3
30 u"	10.0	8	19.5	20	22.45	39	21.65	64	5-2384214-2
30 u"	10.0	8	12.5	6	8.45	25	7.65	36	5-2384214-1
15 u"	86.5	8	44.5	70	72.45	89	71.65	164	4-2384214-8
15 u"	53.5	8	28	37	39.45	56	38.65	98	4-2384214-7
15 u"	36.5	8	19.5	20	22.45	39	21.65	64	4-2384214-6
15 u"	22.5	8	12.5	6	8.45	25	7.65	36	4-2384214-5
15 u"	10.0	8	44.5	70	72.45	89	71.65	164	4-2384214-4
15 u"	10.0	8	28	37	39.45	56	38.65	98	4-2384214-3
15 u"	10.0	8	19.5	20	22.45	39	21.65	64	4-2384214-2
15 u"	10.0	8	12.5	6	8.45	25	7.65	36	4-2384214-1
G/F	86.5	8	44.5	70	72.45	89	71.65	164	3-2384214-8
G/F	53.5	8	28	37	39.45	56	38.65	98	3-2384214-7
G/F	36.5	8	19.5	20	22.45	39	21.65	64	3-2384214-6
G/F	22.5	8	12.5	6	8.45	25	7.65	36	3-2384214-5
G/F	10.0	8	44.5	70	72.45	89	71.65	164	3-2384214-4
G/F	10.0	8	28	37	39.45	56	38.65	98	3-2384214-3
G/F	10.0	8	19.5	20	22.45	39	21.65	64	3-2384214-2
G/F	10.0	8	12.5	6	8.45	25	7.65	36	3-2384214-1
30 u"		NA	44.5	70	72.45	89	71.65	164	2-2384214-4
30 u"		NA	28	37	39.45	56	38.65	98	2-2384214-3
30 u"		NA	19.5	20	22.45	39	21.65	64	2-2384214-2
30 u"		NA	12.5	6	8.45	25	7.65	36	2-2384214-1
15 u"		NA	44.5	70	72.45	89	71.65	164	1-2384214-4
15 u"		NA	28	37	39.45	56	38.65	98	1-2384214-3
15 u"		NA	19.5	20	22.45	39	21.65	64	1-2384214-2
15 u"		NA	12.5	6	8.45	25	7.65	36	1-2384214-1
G/F		NA	44.5	70	72.45	89	71.65	164	2384214-4
G/F		NA	28	37	39.45	56	38.65	98	2384214-3
G/F		NA	19.5	20	22.45	39	21.65	64	2384214-2
G/F		NA	12.5	6	8.45	25	7.65	36	2384214-1
PRECIOUS PLATING THICKNESS (TOTAL)	W	V	J	N	C	B	A	POS.	PART NUMBER
	MYLAR SIZE (PAGE 4)								

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH

-

-

DWN SANDERS, YAN 14DEC2020

CHK MIKE.CHEN 14DEC2020

APVD HOPE LU 14DEC2020

PRODUCT SPEC 108-160247

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB AND CENTER POST

SIZE A2

CAGE CODE 00779

DRAWING NO C-2384214

RESTRICTED TO -

SCALE 6:1



SHEET 2 OF 6

REV B

1471-9 (3/13)

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14DEC2020 SANDERS, YAN	TE Connectivity	
DIMENSIONS:		CHK 14DEC2020 MIKE, CHEN		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 14DEC2020 HOPE, LU	NAME	
0 PLC ±		PRODUCT SPEC	PCI EXPRESS CARD EDGE CONNECTOR	
1 PLC ±0.3		APPLICATION SPEC	GEN5, 1.5 SOLDER TAB AND CENTER POST	
2 PLC ±0.20		WEIGHT	SIZE	
3 PLC ±0.050		CUSTOMER DRAWING	CAGE CODE	
4 PLC ±		SCALE 6:1	DRAWING NO	
ANGLES ±		SHEET 3 OF 6	RESTRICTED TO	
FINISH		REV B		

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FRONT VIEW




36POS AS SHOWN
SCALE 4:1

FRONT VIEW




64POS AS SHOWN
SCALE 4:1

FRONT VIEW



98POS AS SHOWN
SCALE 4:1

FRONT VIEW




164POS AS SHOWN
SCALE 4:1

W
REF

V
REF

J




MYLAR SIZE
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ANGLES ±-

FINISH

-

-

DWN SANDERS YAN 14DEC2020

CHK MIKE CHEN 14DEC2020

APVD HOPE LU 14DEC2020

PRODUCT SPEC 108-160247

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME PCI EXPRESS CARD EDGE CONNECTOR GEN5, 1.5 SOLDER TAB AND CENTER POST

SIZE A2

CAGE CODE 00779

DRAWING NO C-2384214

RESTRICTED TO -

SCALE 6:1

SHEET 4 OF 6

REV B

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A

A




HARD TRAY: FOR 164POS
SCALE 1:2



HARD TRAY: FOR 98POS
SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS, YAN CHK MIKE, CHEN APVD HOPE, LU	14DEC2020 14DEC2020 14DEC2020	TE Connectivity		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		PCI EXPRESS CARD EDGE CONNECTOR		
mm	0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-160247		GEN5, 1.5 SOLDER TAB AND CENTER POST		
MATERIAL	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-	-	A2	00779	C-2384214	-	
-	-	CUSTOMER DRAWING		SCALE	SHEET	REV
				6:1	5 OF 6	B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SOFT TRAY: FOR 64POS
SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
SANDERS, YAN
CHK
MIKE, CHEN
APVD
HOPE, LU

14DEC2020
14DEC2020
14DEC2020

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±0.050

4 PLC ±

ANGLES ±

FINISH

MATERIAL

-

-

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN5, 1.5 SOLDER TAB AND CENTER
POST

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2384214

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
6:1

SHEET
6 OF 6

REV
B

TE Connectivity

1471-9 (3/13)