







N= Number of Poles
Dimension Dim A. B

Dim A	$N \times 10.0 + 2.0$
Dim B	$(N-1) \times 10.0$



SIGN	DATE	DESCRIPTION	APPROVER
△	11/13'12	Change the screw plating specification	Guoxue
△	11/13'12	Change the dimensional tolerance	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:	300 V, 25 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	8.8 Lb-In.
WIRE RANGE:	22 - 12 AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS:	STEEL, M3.5

APPROVAL: 
Critical dimension: 

Part No.:

YK 615 xx 0 x x 00G		RoHS compliant (lead<4%) In copper Alloy
NO. OF POLES	MARK	0: "A" MAK
02: 2 POLES	1: "ANY" MAK	
03: 3 POLES		
04: 4 POLES		
...		
30: 30 POLES		
	TERMINAL & SCREW PLATED	
	0: TERMINAL & SCREW: G/F	
	△ 1: TERMINAL: G/F, SCREW: ZINC	
	2: TERMINAL: SN, SCREW: G/F	
	△ 3: TERMINAL: SN, SCREW: ZINC	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-615 W/O Flange Series			
PART NO.	YK615xx0xx00G			DWG NO.	8YK0001-615
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2012.12.01	Guoxue 2012.12.01		Tolerance
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: C	X° ±1°