


Actuator

704.040.2



<https://eao.com/p/704.040.2>

Your product:



704.040.2 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29 mm
Front bezel material:	Plastic
Front bezel colour:	Grey

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens shape:	flush
Lens optics:	transparent
Lens colour:	Red
Lens material:	Plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Operating Travel:	ca. 5.8 mm ± 0.2 mm
Mechanical lifetime:	≤3 Mio. cycles of operation
Operating force:	8 N

Switching action: Maintained

Weight: 0.04 kg

AMBIENT CONDITION

Storage temperature: – 40 °C ... + 85 °C

Operating temperature: – 40 °C ... + 55 °C

IP Protection: IP65 front side

OTHER

Housing colour: Grey


Short Description: Actuator, Ø 29 mm, flush, non illuminative, Red, Plastic, transparent, round, Grey, Plastic, Maintained

Hints: Frontring with protective cover to be mounted with a torque of 0.4 Nm onto actuator, Max. 3 switching elements can be clipped on


max. number of switching elements: 3

Housing material: Plastic

Wiring diagrams:




Dimension drawings:



A = Screw terminal

Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm