







PCB LAYOUT
Top view

△
N=Number of Poles
Dim.P=(N-1)×5.08
Dim.L=N×5.08+1.0

△ Dim. \ Poles	1P	2P-6P	7P-12P	12P-18P	19P-24P
Dim.L	±0.10	±0.20	±0.25	±0.30	±0.40
Dim.P		±0.15	±0.20	±0.25	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	10/30'09	The dimension changed from 19.1 to 19.1±0.50	Kind
△	10/30'09	Add tolerance table for Dim.L and Dim.P	Kind
△	10/30'09	Terminal lever material changed to thermoplastic (UL94-HB)	Kind
△	04/23'13	update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Solder pin : Brass , Tin plated
- Item 2 Wire guard : Stainless steel
- Item 3 Terminal housing: Thermoplastic (UL94V-0)
- Item 4 Terminal cover: Thermoplastic (UL94V-0)
- △ ● Item 5 Terminal lever: Thermoplastic (UL94V-HB)

- Electrical cULus
- Voltage rating: 300V
 - Current rating: 15A
 - Wire range:
 - Solid wire(AWG): 12-28
 - Stranded wire(AWG): 12-28
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - △ ● Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus
 - Critical dimension: △

HT xx 30 x 0 xxxx G

- △
- 01 1 CONTACTS
 - 02 2 CONTACTS
 -
 - 24 24 CONTACTS

- △ Color
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors

- △ G: RoHs compliant (lead<4%) In copper Alloy
- 000 0 Standard @ Logo
 - 000 A Standard ANY Logo
 - 009 1 Standard ANY Logo
 - Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HT-5.08 Series				
PART NO.	HTxx30x0xxxxG			DWG NO.	8HT0101	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Da cheng 2013.04.23	Da cheng 2013.04.23		Tolerance	
					X.	±0.50
				UNIT: mm	X.X	±0.30
				SCALE: NONE	X.XX	±0.10
SHEET: 01/01	REV: D	X°	±1°			