




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER ECO 21-002470	3-24-21	CT	DH



- 1 MATERIAL: STAINLESS STEEL (303)
- 2 FINISH: PASSIVATED
- 3 KEY HOLE ORIENTATION (DIM A) PER MATING GUIDE MODULE PART NUMBER TABLE (ORIENTATION SHOWN ON PCB LAYOUT IS FOR 1-2000677-2 OR 2000713-2)
- 4 ANNULAR RING PLATED AROUND GUIDE PIN MOUNTING HOLE ON TOP AND BOTTOM SIDE OF BOARD
- 5 PRELIMINARY-NOT RELEASED FOR PRODUCTION



5	10-32 UNF	15	7.25	4.20	2-2000676-5
	10-32 UNF	15	7.25	5.70	2-2000676-4
	10-32 UNF	19	38.10	5.70	2-2000676-3
	10-32 UNF	24	38.10	5.70	2-2000676-2
	10-32 UNF	19	31.70	5.70	2-2000676-1
5	10-32 UNF	24	12.70	3.30	2-2000676-0
	10-32 UNF	24	31.75	5.70	1-2000676-9
	10-32 UNF	24	10.35	4.95	1-2000676-8
	10-32 UNF	19	10.35	4.95	1-2000676-7
	10-32 UNF	24	9.00	1.32	1-2000676-6
5	10-32 UNF	24	5.40	2.60	1-2000676-5
	10-32 UNF	24	18.00	5.70	1-2000676-4
	10-32 UNF	19	7.25	5.70	1-2000676-3
	10-32 UNF	19	7.25	4.20	1-2000676-2
	10-32 UNF	19	7.25	1.32	1-2000676-0
5	M5X.8-6g	24	6.30	2.40	2000676-9
	M5X.8-6g	19	9.00	3.40	2000676-8
	M5X.8-6g	24	9.00	3.40	2000676-7
	10-32 UNF	24	10.35	5.70	2000676-6
	10-32 UNF	24	7.25	7.30	2000676-5
5	10-32 UNF	24	7.25	5.70	2000676-4
	10-32 UNF	24	7.25	4.20	2000676-3
	10-32 UNF	24	7.25	2.60	2000676-2
	10-32 UNF	24	7.25	1.32	2000676-1
	DIM M THREAD	DIM L	DIM K	DIM J	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±0.5

±0.13

±0.013

±

±

TOLERANCES UNLESS OTHERWISE SPECIFIED:

PRODUCT SPEC

108-2072

APPLICATION SPEC

114-13056

WEIGHT

CUSTOMER DRAWING

DWN

McALONIS, M.

10JAN08

CHK

McALONIS, M.

10JAN08

APVD

McALONIS, M.

10JAN08

NAME

KEYED GUIDE PIN, MACHINED BACKPLANE CONNECTOR, MULTIGIG, THREADED POST

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A

100779

C=2000676

SCALE

8:1

SHEET

1





OF

2

REV

N

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



W/O ESD SPRING	NO KEY	2-2000677-9
W/O ESD SPRING	315°	2-2000677-8
W/O ESD SPRING	270°	2-2000677-7
W/O ESD SPRING	90°	2-2000677-3
W/O ESD SPRING	45°	2-2000677-2
W/O ESD SPRING	0°	2-2000677-1
W/O ESD SPRING	0°	2-2000677-0
W/O ESD SPRING	NO KEY	1-2000677-9
W/O ESD SPRING	315°	1-2000677-8
W/O ESD SPRING	270°	1-2000677-7
W/O ESD SPRING	90°	1-2000677-3
W/O ESD SPRING	45°	1-2000677-2
W/ESD SPRING	NO KEY	2000713-6
W/ESD SPRING	315°	2000713-5
W/ESD SPRING	270°	2000713-4
W/ESD SPRING	90°	2000713-3
W/ESD SPRING	45°	2000713-2
W/ESD SPRING	0°	2000713-1
ESD SPRING	DIM T	20.3mm GUIDE MODULE
MATING GUIDE MODULE		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN McALONIS, M.	10JAN08	TE Connectivity	
		CHK McALONIS, M.	10JAN08		
DIMENSIONS:		APVD McALONIS, M.	10JAN08	NAME	
mm		PRODUCT SPEC		KEYED GUIDE PIN, MACHINED	
		108-2072		BACKPLANE CONNECTOR,	
		APPLICATION SPEC		MULTIGIG, THREADED POST	
		114-13056		SIZE	
		WEIGHT		A100779C=2000676	
MATERIAL		FINISH		CUSTOMER DRAWING	
-		-		SCALE 1:1 SHEET 2 OF 2 REV N	