








DIM		TOL			
		2P-6P	7P-12P	13P-18P	19P-24P
Dim L	(N-1)×5.08+7.08	±0.15	±0.25	±0.30	±0.40
Dim B	(N-1)×5.08	±0.15	±0.25	±0.30	±0.40
Dim C	N×5.08	+0.0 -0.20		+0.0 -0.40	
Dim D	(N-1)×5.08	±0.15	±0.25	±0.30	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	01/10/09	The design is changed	Jacke
△	04.20/09	The operating temperature is changed	Jacke
△	2010.01.12	Add cULus standard	Jacke
△	2010.03.31	Add the 2p mark	Jacke
△	2010.04.26	The current rating is changed from 10A to 20A	Jacke
△	2014.09.27	The current rating is changed from 20A to 10A	Evan
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item① Terminal body:Thermoplastic (UL94V-0)

Item② Female contact:PhBz(CuSn), Tin plated

Item③ Terminal cover:Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ∇

V7 xx 5 1 x 1 xxxx G

No. OF POLES
02 2 ploe
03 3 ploe
...
24 24 ploe

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy
0000: "@ " Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

Amphenol
ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	V7 5.08 Series Right-angle				DWG NO.	8V70302		
PART NO.	V7xx51x1xxxxG				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance		
		Evan 2014.09.27	Evan 2014.09.27			UNIT: mm	X.	±0.5
						SCALE: NONE	X.X	±0.3
						REV.: G	X.XX	±0.1
							X°	±1°

SHEET: 01/01