



DESCRIPTION: 1B // QUIK-LOQ // M // PANEL MOUNT // SOLDER CUP // NON-LATCH*



821BYYY-103R001

SERIES
POSITIONS
YYY = SEE POSITION CHART
GENDER
1 = MALE
TYPE
0 = SOLDER CUP PANEL MOUNT (NON-LATCH)
KEY ORIENTATION
3 = 1 KEY // 0°
CONTACT PLATING
1 = 7μ" GOLD PLATED

SPECIFICATIONS:

MATERIALS:

SHELL: NICKEL/CHROME PLATED BRASS
CONTACTS: 7u" GOLD PLATED BRASS
NUT: NICKEL/CHROME PLATED BRASS
INSULATOR: PPS (HIGH TEMPERATURE)

MECHANICAL:

MATING CYCLES: 5000 CYCLES
OPERATING TEMPERATURE: -40°C TO +200°C
PROCESS TEMPERATURE: 260°C FOR 5 SECONDS
SHIELDING: 75dB @ 10MHz // 40dB @ 1GHz
IP RATING: 50
MAX TORQUE: 4.5 Nm

POSITION CHART // ELECTRICAL/WIRE SPECIFICATIONS

*solder side view of insulator

POSITIONS	CONTACTS*	CONTACT Ø	MAX CONTACT mΩ	WORKING VOLTAGE	MAX AMPERAGE	MAX WIRE AWG
002		1.30mm	5.0 mΩ	500 V	15.0 A	20
003		1.30mm	5.0 mΩ	430 V	12.0 A	20
004		0.90mm	6.0 mΩ	430 V	10.0 A	22
005		0.90mm	6.0 mΩ	415 V	9.0 A	22
006		0.70mm	7.5 mΩ	350 V	7.0 A	24
007		0.70mm	7.5 mΩ	315 V	7.0 A	24
008		0.70mm	7.5 mΩ	315 V	5.0 A	24
010		0.50mm	10.0 mΩ	300 V	2.5 A	28
014		0.50mm	10.0 mΩ	260 V	2.0 A	28

*WILL NOT LATCH WITH NORCOMP 821B SERIES FEMALE CABLE MOUNT CONNECTORS DUE TO NO LATCH MECHANISM WITHIN CONNECTOR.

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
02/05/2016

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV
5

DWG NO.

821BYYY-103R001