




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a :Terminal body Thermoplastic (UL94 V-0)
- Item b :Terminal body Thermoplastic (UL94 V-0)
- Item c :Male contact pin: Brass Tin plated
- Item d :Spring clamp: Stainless steel
- Item e :Pad board: Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:



SECTION A-A

NB xx A 0 x 0 xxxxx G

02 2 poles
03 3 poles
... ..
16 16 poles

0 Black
5 Green
6 Blue
8 Grey
(RAL 7035/D)

any special item by
customer request,
please contact sales
department.

N = Number of poles

Dim A=Nx7.5-1.0

Dim B=Nx7.5+0.7


Dim C=(N-1)x7.5

	Dim A	Dim B	Dim C
2-6p	±0.20	±0.20	±0.10
7-12p	±0.30	±0.30	±0.20
13-16p	±0.40	±0.40	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NB 7.5mm series W/O Flange						
PART NO.	NBxxA0x0xxxxG			DWG NO.	8NB0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Runner 2010.06.10	Runner 2010.06.10		Tolerance		
					UNIT: mm	X.	±0.50
					SCALE: 2/1	X.X	±0.30
					REVISION: A	X.XX	±0.10
				SHEET: 01/01		X°	±1°