





Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	12.7	17.7	22.7	27.7	32.7	37.7	42.7	47.7	52.7	57.7	62.7	67.7
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	± 0.15					± 0.20						± 0.25
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	72.7	77.7	82.7	87.7	92.7	97.7	102.7	107.7	112.7	117.7	122.7	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	± 0.25					± 0.30						

SIGN	DATE	DESCRIPTION	APPROVER
△	10/28/08	The temperature changed from -40°C to +115°C	Kind
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Male contact pin: Brass(CuZn),Tin or Au plated.
- Item② Terminal (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- ⚠ ● Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

EX xx 0 x x 0 xxxx G

02 2 CONTACTS 0 Tin plating
03 3 CONTACTS 1 G/F plating
... ..
24 24 CONTACTS

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

000 0 Standard Pb < 40,000ppm
Any special item by
customer request,
please contact sales
department. (RoHS)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EX 5.0 Series 2P-24P					
PART NO.		EXxx0xx0xxxxG		DWG NO.		8EX0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Kind 2008.10.28	Kind 2008.10.28		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV: C	X.XX	±0.10
						X°	±1°