



DIMENSION

Dim A	(N-1)X5.08+6.58
Dim B	(N-1)X5.08
Dim C	(N+1)X5.08+5.04

N = Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40



V8 xx 51 x 1 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

G RoHS compliant
(lead<4%)
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

SIGN	DATE	DESCRIPTION	APPROVER
⚠	08.10.17	The dimension is changed from 5.2mm to 5.08mm	Seamus
⚠	2009.10.30	The design is changed from the round hole to hexagonal hole.	Seamus
⚠	2009.10.30	The Torque is changed	Jacke
⚠	2010.01.15	Add cULus standard	Jacke
⚠	2010.08.24	The design is changed	Jacke
⚠	2010.08.24	The design is changed	Jacke
⚠	2010.09.27	Add the dimension	Jacke
⚠	07/10`12	Change the material of contact from Brass to Copper	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item Ⓐ Terminal(housing):Thermoplastic (UL94V-0)
- Item Ⓑ Terminal (Cover):Thermoplastic (UL94V-0)
- Item Ⓒ Terminal screw:Steel Zinc plating "-" slot type
- Item Ⓓ Clamp:Brass(CuZn), Ni plating
- Item Ⓔ Male Contact Pin: Copper, Tin plated
- Item Ⓕ Flange nut: Brass M2.5

Electrical

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 4Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension: ∇

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V8 5.08 Series With flange Nut type							
PART NO.		V8xx51x1xxxxG			DWG NO.		8V80302		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Chen Bo 07/10`12	Chen Bo 07/10`12		UNIT: mm			X. ±0.50	
					SCALE: NONE			X.X ±0.30	
					REV.: H			X.XX ±0.10	
				SHEET: 01/01				X° ±1°	