




SECTION P-P

Dimension

Dim L	$N \times 10.16 + 3.04$
Dim B	$(N-1) \times 10.16$
Dim C	$(N-1) \times 10.16$

N=Number of poles

POLES	TOL
2p-5p	± 0.25
6p-8p	± 0.35
9p-12p	± 0.45



SIGN	DATE	DESCRIPTION	APPROVER
	03/04`14	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a Terminal(housing): Thermoplastic,UL 94 - V0.
- Item b Male contact pin: Copper, Gold plated

Electrical: cULus / IEC

- Voltage rating: 300V / 1000V
- Current rating: 55A / 76A
- Withstanding Voltage: 1.6 KV / 8 KV
- Operating temperature: -40°C to $+115^{\circ}\text{C}$
- Soldering temperature: $260^{\circ}\text{C} \pm 5^{\circ}\text{C} / 5 \text{ Sec}$
- Safety Approval:
- Critical dimension:

EW xx 61 x 2 xxxx G		G RoHS compliant (lead<4%) In copper Alloy	
Solid Block		Color	0000 Standard @ Logo
02 2Contacts		0 Black (RAL9005)	000A Standard ANY Logo
03 3Contacts		2 Red (RAL3001/D)	Any special item by customer request, please contact sales department.
12 12Contacts		3 Orange(RAL2011/P)	
		4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EW 10.16 Series 2p-12p Right -Angle (up)				
PART NO.	EWxx61x2xxxxG		DWG NO.	8EW0002	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Chen Bo 03/04`14	Chen Bo 03/04`14		X. ± 0.50 X.X ± 0.30 X.XX ± 0.10 X° $\pm 1^{\circ}$
					UNIT: mm SCALE: NONE
				SHEET: 01/01	REV.: C