


Actuator

704.117.0



<https://eao.com/p/704.117.0>

Your product:



704.117.0 Actuator

FRONT

Front dimension:	Ø 29 mm
Front bezel material:	Aluminium
Front bezel colour:	Nature

MOUNTING

Design:	raised
---------	--------

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Weight:	0.07 kg
Switching angle:	42° left / 42° right
Switching positions:	3 positions
Switching action:	Maintained (a) - Rest - Momentary
Mechanical lifetime:	≤50 000 cycles of operation

AMBIENT CONDITION

Operating temperature:	- 40 °C ... + 55 °C
IP Protection:	IP65 front side
Storage temperature:	- 40 °C ... + 85 °C

OTHER

Short Description:

Actuator, Ø 29 mm, Nature, Aluminium, Maintained (a) - Rest - Momentary


Hints:

The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on


max. number of switching elements:

3

Switching positions:



Dimension drawings:




A = Screw terminal

Wiring diagrams:



Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm