

## SUMMARY

### # Wires

Low voltage 4



*Image is for illustrative purpose only*

|                  |                                    |
|------------------|------------------------------------|
| Series           | 0E                                 |
| Termination type | Female solder                      |
| IP rating        | 68                                 |
| AWG wire size    | 32.00 - 24.00                      |
| Cable Ø          | 3.10 - 3.50 mm                     |
| Status           | active                             |
| Matching parts   | <a href="#">FFA.0E.304.CLAC35Z</a> |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | PCA*: Free receptacle, cable collet and nut for fitting a bend relief                                                         |
| Keying            | Hermaphroditic keying (half moon insert) with female pin 1                                                                    |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Variant           | Z : Nut for fitting a bend relief                                                                                             |
| Weight            | 15.04 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 0E.304 : 4 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 7 Amps                    |

### Specifications

Contact Type: Solder  
Contact Dia.: 0.7 mm (0.028in)  
Bucket Dia.: 0.6 mm (0.024in)  
Max. Solid Conductor: 0.25 mm<sup>2</sup> (AWG 24)  
Max. Stranded Conductor: 0.14 mm<sup>2</sup> (AWG 26)  
R (max): 6.1 mOhm


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest: 1060 V (AC), 1500 V (DC)

Others

- Endurance (Shell): 5000 mating cycles
- Temp (min / max): -55°C / +200°C
- Humidity (max): <=95% [at 60 deg C / 140 F]
- Vibration: 15 g [10 Hz - 2000 Hz]
- Shock Resistance: 100 g [ 6 ms]
- Climatical Category: 50/175/21
- Shielding (min): 95 dB (10 MHz)
- Shielding (min): 80 dB (1 GHz)
- Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | L    | S2   |
|-----|------|------|------|
| mm. | 13   | 34   | 7    |
| in. | 0,51 | 1,34 | 0,28 |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Spanner wrench: [DCD.OE.007.PA070](#)

Cables

|                    |      |       |                                                                                     |
|--------------------|------|-------|-------------------------------------------------------------------------------------|
| CMN.04.T28.031PGCE | PVC  | GREY  |  |
| CMN.04.T28.031PGZE |      | Grey  |  |
| CMN.04.T28.031PNCE | PVC  | Black |  |
| CMN.04.T28.031PNZE |      |       |  |
| CMN.04.T28.031QGC  | TPR  | Grey  |                                                                                     |
| 4260               | PTFE | White |  |

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.