



SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material:

- Item a :Terminal body Thermoplastic (UL94 V-0)
- Item b :Terminal body Thermoplastic (UL94 V-0)
- Item c :Male contact pin: Brass Tin plated
- Item d :Spring clamp: Stainless steel

Electrical

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +105°C
- Safety Approval: 



SECTION A-A

NB xx 7 0 x 4 xxxx G

02 2 poles
03 3 poles
... ..
24 24 poles

0 Black
5 Green
(RAL6018/T)
6 Blue
8 Grey
(RAL7035/D)

RoHS
Pb<40,000ppm

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

N = Number of poles

Dim A=Nx5.0+1.5

Dim B=Nx5.0+3.2


Dim C=(N-1)x5.0

	Dim A	Dim B	Dim C
2-6p	±0.20	±0.20	±0.20
7-12p	±0.25	±0.25	±0.25
13-18p	±0.30	±0.30	±0.30
19-24p	±0.40	±0.40	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NB 5.0mm series (With snap-in mounting feet)									
PART NO.	NBxx70x4xxxxG				DWG NO.	8NB0007				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance	
		runner 2007.12.04	runner 2007.12.04		UNIT: mm		X. ±0.50			
					SCALE: 2/1		X.X ±0.30			
					SHEET: 01/01		REV.: B		X.XX ±0.10	
						X° ±1°				