







N=NUMBER OF POLES

Dim L	(N-1)×5.0+6.0
Dim B	(N-1)×5.0

	TOL				
	1--4P	5--9P	10--14P	15--19P	20--24P
Dim L	±0.15	±0.20	±0.30	±0.40	±0.50
Dim B	±0.15	±0.20	±0.30	±0.40	±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	2/26'07	The Soldering temperature from 245° to 250°	Aaron
△	7/17'09	Operating Tem.changed to -40°C ~ 115°C	Kind
△	7/17'09	Current rating changed from 7A to 6A	Kind
△	05/23'11	Current rating is changed from 6A to 8A	Steven

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Insulating body Thermoplastic (UL94V-0)
- Item 2 Insulating cover Thermoplastic (UL94V-0)
- Item 3 Insulating lever Thermoplastic (UL94V-0)
- Item 4 Contact pin Brass, Tin plated
- Item 5 Spring clamp Stainless steel

Electrical cULus

- Voltage rating:300V
- △ ● Current rating:8A
- Wire range:
 - Solid wire(AWG):16-26
 - Stranded wire(AWG):16-26
 - Wire strip length:6-7mm
 - Withstanding Voltage:1.6KV
- △ ● Operating temperature:-40°C to +115°C
- △ ● Soldering temperature:250°C±10°C/5 Sec
- Safety Approval:
- Critical dimension:

PART NO.

HX xx 00 x 0 xxxx G

Poles	0	Black	0000 Standard @ Logo
01 1Contacts	2	Red	000A Standard ANY Logo
02 2Contacts	3	Orange	Any special item by
... ..	5	Green(RAL6018/T)	customer request,
24 24Contacts	8	Grey(RAL7004/P)	please contact sales
	9	White	department.
	C	Multiple colors	

RoHS
Pb<40,000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HX 5.0 Series Vertiac (90° Wire inlet)				
PART NO.	HXxx00x0xxxxG			DWG NO.	8HX0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		STEVEN 2011.05.23	STEVEN 2011.05.23		Tolerance
					X. ±0.50
					X.X ±0.30
				UNIT: mm	X.XX ±0.10
				SCALE: NONE	X° ±1°
				SHEET: 01/01	REV.: G