







P.C.B Layout

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	±0.15					±0.20					±0.25	
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	±0.25					±0.30						

SIGN	DATE	DESCRIPTION	APPROVER
△	05/20.08	螺絲孔和螺絲進行設置變更	Aaron
△	05/20.08	增加cULus	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal cover :Thermoplastic (UL94V-0)
- Item② Terminal housing : Thermoplastic (UL94V-0)
- Item③ Terminal screw : Steel Zinc plating "- " slot type
- Item④ Wire guard solder pin : Brass, Tin plated
- Item⑤ Clamp : Steel stamping, Zinc plating

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

PART NO.

EQ xx 05 x 0 xxxx G			RoHS Pb<40,000ppm
Poles	Color		0000 Standard @ Logo
02 2Contacts	0 Black		000A Standard ANY Logo
03 3Contacts	5 Green		Any special item by
.....	(RAL 6018/T)		customer request,
24 24Contacts	6 Blue		please contact sales
	8 Grey		department.
	(RAL 7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EQ 5.0 Series 90 D Wire inlet (Vertical)									
PART NO.		EQxx05x0xxxxG				DWG NO.		8EQ0003			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance				
			Aaron 2008.05.20	Aaron 2008.05.20			UNIT: mm		X.	±0.50	
							SCALE: NONE		X.X	±0.30	
					SHEET: 01/01		REV.: C	X.XX	±0.10		
											X*