



Series 801 "Mighty Mouse" Double-Start ACME Threads PCB Receptacle Ordering Information

801-011



Series 801 Printed
Circuit Board Receptacle

These receptacles feature a low profile shell for minimum protrusion inside enclosures. Contacts are non-removable. Connectors are backfilled with epoxy for a watertight seal.

Two Shell Styles: jam nut with o-ring for rear panel mounting, or square flange.

PCB Contacts feature gold-plated tails for solder termination to rigid or flexible circuits.

Solder Cup Contacts are factory-installed and fully sealed with epoxy.


HOW TO ORDER

Sample Part Number

801-011	-07	M	7-10	P	A		
Series	Shell Style	Shell Material / Finish	Shell Size- Insert Arrangement	Contact Type	Shell Key Position		
801-011 Receptacle for Solder Cup or PCB Termination	-02 Square Flange	C Aluminum / Black Anodize (Non-Conductive) RoHS Compliant	No. of Contacts Arr. #23 #20 #16 #12 5-3 3 1 6-1 4 1 6-4 4 2 6-7 7 1 7-1 10 2 7-10 13 2 8-2 4 2 8-13 19 4 8-200 4 2 9-4 8 2 9-19 26 5 9-200 12 1 9-201 4 2 10-5 8 2 10-26 37 2 10-200 6 2 10-201 10 2 10-202 10 5 13-2 55 7 13-3 17 14 13-7 85 12 13-37 21 22 13-200 21-130 130	P Pin, PC Tail S Socket, PC Tail E Pin, Solder Cup F Socket, Solder Cup	A Normal Alternate Key Positions: B C D E F		
		M Aluminum / Electroless Nickel RoHS Compliant					
		NF Aluminum / Cadmium with Olive Drab Chromate					
		ZN Aluminum / Zinc-Nickel with Olive Drab Chromate					
		UCR Aluminum / Zinc-Cobalt with Black Chromate RoHS Compliant					
		ZNU Aluminum / Zinc-Nickel with Black Chromate					
		MT Aluminum / Nickel-PTFE RoHS Compliant					
		Z1 Stainless Steel / Passivated RoHS Compliant					
		-07 Jam Nut					


A diagram of a circular shell with contact points. Two key positions are indicated: A° and B°. The diagram shows the internal structure of the shell and the arrangement of the contacts.

	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°



	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

Series 801 Receptacles With PCB or Solder Cup Contacts



DIMENSIONS

Shell Size	Ø A		B Flat		C Flat		D Thread	E Thread UN-2A	Ø F		G Max		H BSC		Ø J		Ø K		Ø L Tail Dia.
	In.	mm.	In.	mm.	In.	mm.			In.	mm.	In.	mm.	In.	mm.	In.	mm.	±.003	±0.08	
5	.575	14.61	.350	8.89	.545	13.84	.3125-.05P-.1L-2A	.3750-28	.244	6.20	.530	13.46	.363	9.22	.680	17.27	.093	2.36	#23
6	.635	16.13	.410	10.41	.595	15.11	.375-.05P-.1L-2A	.4375-28	.330	8.38	.590	14.99	.423	10.74	.750	19.05	.093	2.36	.018/.022
7	.755	19.18	.536	13.61	.723	18.36	.4375-.05P-.1L-2A	.5625-32	.432	10.97	.650	16.51	.483	12.27	.850	21.59	.093	2.36	(0.46/0.56)
8	.755	19.18	.563	14.30	.723	18.36	.5000-.05P-.1L-2A	.5625-32	.493	12.52	.712	18.08	.545	13.84	.938	23.83	.128	3.25	#16
9	.830	21.08	.596	15.14	.790	20.07	.5625-.05P-.1L-2A	.6250-28	.551	14.00	.850	21.59	.607	15.42	1.125	28.58	.128	3.25	.060/.064
10	.890	22.61	.658	16.71	.855	21.72	.6250-.05P-.1L-2A	.6875-28	.620	15.75	.890	22.61	.670	17.02	1.188	30.18	.128	3.25	(1.52/1.63)
13	1.078	27.38	.845	21.46	1.044	26.52	.8125-.1P-.2L-2a	.875-28	.703	17.86	1.030	26.16	.812	20.62	1.375	34.93	.128	3.25	#12
16	1.264	32.11	1.022	25.96	1.230	31.24	1.000-.1P-.2L-2A	1.0625-20	.863	21.92	1.219	30.96	.981	24.92	1.625	41.28	.128	3.25	.092/.096
17	1.325	33.66	1.096	27.84	1.290	32.77	1.062-.1P-.2L-2A	1.125-28	.912	23.16	1.280	32.51	1.060	26.92	1.700	43.18	.128	3.25	(2.34/2.44)

SERIES 801 PANEL CUTOUT

Shell Size	Ø A		Ø B		Ø C		D Flat		Ø E	
	In.	mm.	In.	mm.	In.	mm.	±.002	± 0.05	In.	mm.
5	.330	8.38	.363	9.22	.093	2.36	.360	9.14	.385	9.78
6	.390	9.91	.423	10.74	.093	2.36	.420	10.67	.448	11.37
7	.450	11.43	.483	12.27	.093	2.36	.551	14.00	.573	14.55
8	.510	12.95	.545	13.84	.093	2.36	.551	14.00	.573	14.55
9	.575	14.61	.607	15.42	.128	3.25	.609	15.47	.635	16.13
10	.640	16.26	.670	17.02	.128	3.25	.671	17.04	.698	17.73
13	.825	20.96	.812	20.65	.128	3.25	.859	21.82	.885	22.48
16	1.015	25.78	.981	24.92	.128	3.25	1.038	26.37	1.075	27.31
17	1.075	27.31	1.060	26.92	.128	3.25	1.111	28.22	1.135	28.83