


RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 12mm


SWITCH FUNCTION	
POS. 1	POS. 2
1-2 ON 3-4 OFF	1-2 OFF 3-4 ON




▲ SPDT ON-OFF / OFF-ON
CONTACT CONFIGURATION

NOTE:



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 2A @ 48VDC
5. ILLUMINATION VOLTAGE: N/A
6. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
7. INSULATION RESISTANCE: 1,000M Ω @ 500VDC
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. ELECTRICAL LIFE: 50,000 CYCLES
10. OPERATING TEMPERATURE: -20°C to 55°C
11. INGRESS PROTECTION: IP65
12. SUPPLIED HARDWARE: O-RING AND HEXNUT
13. ▲ DENOTES CRITICAL PARAMETER



▲ FLAT ACTUATOR
BLACK ANODIZED



▲ BODY
BLACK ANODIZED



TERMINALS
1 and 2

TERMINALS
3 and 4



TITLE PV7F2T011

A	23988	RELEASE	8/12/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1:1	DATE 8/12/2019	DR MW	DWG 52-PV7F2T011	REV A
--------------	-------------------	----------	---------------------	----------