

**Features**

- HCMOS Output
- Stabilities to  $\pm 20$  PPM
- Temperature Ranges to  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$
- Supply Voltage: 1.8V, 2.5V, 3.3V

| 1.8V ELECTRICAL CHARACTERISTICS                        |                                 |
|--------------------------------------------------------|---------------------------------|
| PARAMETERS                                             | MAX (Unless otherwise noted)    |
| Frequency Range ( $F_0$ )                              | 0.012 ~ 160.000MHz              |
| Storage Temperature Range ( $T_{STG}$ )                | $-55 \sim +125^{\circ}\text{C}$ |
| Supply Voltage ( $V_{DD}$ )                            | $1.8\text{V} \pm 5\%$           |
| Input Current ( $I_{DD}$ )                             |                                 |
| 0.012 ~ 32.000MHz                                      | 5 mA                            |
| >32.000 ~ 70.000MHz                                    | 10 mA                           |
| >70.000 ~ 120.000MHz                                   | 15 mA                           |
| >120.000 ~ 160.000MHz                                  | 30 mA                           |
| Standby Current                                        | 10 $\mu\text{A}$                |
| Output Symmetry (50% $V_{DD}$ )                        | 40% ~ 60%                       |
| Rise/Fall Time (20%/80% $V_{DD}$ Levels) ( $T_R/T_F$ ) |                                 |
| 0.012 ~ 32.000MHz                                      | 5.0 nS                          |
| >32.000 ~ 120.000MHz                                   | 3.5 nS                          |
| >120.000 ~ 160.000MHz                                  | 3.0 nS                          |
| Output Voltage ( $V_{OL}$ )                            | 20% $V_{DD}$                    |
| ( $V_{OH}$ )                                           | 80% $V_{DD}$ Min                |
| Output Load (HCMOS)                                    | 15pF                            |
| Start-up Time ( $T_S$ )                                | 10 mS                           |
| Output Disable Time 1                                  | 300 nS                          |
| Output Enable Time 1                                   | 10 mS                           |

| ENABLE / DISABLE FUNCTION          |                |
|------------------------------------|----------------|
| Pin <sup>1</sup>                   | Output (pin 3) |
| OPEN <sup>1</sup>                  | Active         |
| '1' Level $V_{IH} \geq 70\%V_{DD}$ | Active         |
| '0' Level $V_{IL} \leq 30\%V_{DD}$ | High Z         |

| Available Options by Stability & Operating Temp for 1.8V |                            |                       |
|----------------------------------------------------------|----------------------------|-----------------------|
| Frequency Stability                                      | Operating Temperature (°C) | Frequency Range (MHz) |
| ±100PPM <sup>2</sup>                                     | -10 ~ +70                  | 0.012 ~ 160.000       |
| ±100PPM <sup>2</sup>                                     | -20 ~ +70                  | 0.012 ~ 160.000       |
| ±100PPM <sup>2</sup>                                     | -40 ~ +85                  | 0.012 ~ 160.000       |
| ±50PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 160.000       |
| ±50PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 160.000       |
| ±50PPM <sup>2</sup>                                      | -40 ~ +85                  | 0.012 ~ 160.000       |
| ±25PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 160.000       |
| ±25PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 160.000       |
| ±25PPM <sup>3</sup>                                      | -40 ~ +85                  | 0.012 ~ 160.000       |
| ±20PPM <sup>3</sup>                                      | -10 ~ +70                  | 0.012 ~ 160.000       |
| ±20PPM <sup>3</sup>                                      | -20 ~ +70                  | 0.012 ~ 160.000       |

<sup>1</sup> An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

<sup>2</sup> Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, and one-year aging.

<sup>3</sup> Inclusive of 25°C tolerance and operating temperature rang.

| 2.5V ELECTRICAL CHARACTERISTICS                        |                              |
|--------------------------------------------------------|------------------------------|
| PARAMETERS                                             | MAX (Unless otherwise noted) |
| Frequency Range ( $F_0$ )                              | 0.012 ~ 170.000MHz           |
| Storage Temperature Range ( $T_{STG}$ )                | -55 ~ +125°C                 |
| Supply Voltage ( $V_{DD}$ )                            | 2.5V±5%                      |
| Input Current ( $I_{DD}$ )                             |                              |
| 0.012 ~ 32.000MHz                                      | 7 mA                         |
| >32.000 ~ 50.000MHz                                    | 12 mA                        |
| >50.000 ~ 125.000MHz                                   | 26 mA                        |
| >125.000 ~ 160.000MHz                                  | 35 mA                        |
| >160.000 ~ 170.000MHz                                  | 40 mA                        |
| Standby Current                                        | 10 $\mu$ A                   |
| Output Symmetry (50% $V_{DD}$ )                        |                              |
| 0.012 ~ 50.000MHz                                      | 45% ~ 55%                    |
| >50.000 ~ 200.000MHz                                   | 40% ~ 60%                    |
| Rise/Fall Time (10%/90% $V_{DD}$ Levels) ( $T_R/T_F$ ) | 5 nS                         |
| Output Voltage ( $V_{OL}$ )                            | 10% $V_{DD}$                 |
| ( $V_{OH}$ )                                           | 90% $V_{DD}$ Min             |
| Output Load (HCMOS)                                    | 15pF                         |
| Start-up Time ( $T_S$ )                                | 10 mS                        |
| Output Disable Time 1                                  | 150 nS                       |
| Output Enable Time 1                                   | 10 mS                        |

| ENABLE / DISABLE FUNCTION          |                |
|------------------------------------|----------------|
| Pin <sup>1</sup>                   | Output (pin 3) |
| OPEN <sup>1</sup>                  | Active         |
| '1' Level $V_{IH} \geq 70\%V_{DD}$ | Active         |
| '0' Level $V_{IL} \leq 30\%V_{DD}$ | High Z         |

| Available Options by Stability & Operating Temp for 2.5V |                            |                       |
|----------------------------------------------------------|----------------------------|-----------------------|
| Frequency Stability                                      | Operating Temperature (°C) | Frequency Range (MHz) |
| ±100PPM <sup>2</sup>                                     | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±100PPM <sup>2</sup>                                     | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±100PPM <sup>2</sup>                                     | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±25PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±25PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±25PPM <sup>3</sup>                                      | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±20PPM <sup>3</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±20PPM <sup>3</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |

<sup>1</sup> An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

<sup>2</sup> Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, and one-year aging.

<sup>3</sup> Inclusive of 25°C tolerance and operating temperature rang.

| 3.3V ELECTRICAL CHARACTERISTICS                        |                              |
|--------------------------------------------------------|------------------------------|
| PARAMETERS                                             | MAX (Unless otherwise noted) |
| Frequency Range ( $F_0$ )                              | 0.012 ~ 170.000MHz           |
| Storage Temperature Range ( $T_{STG}$ )                | -55 ~ +125°C                 |
| Supply Voltage ( $V_{DD}$ )                            | 3.3V±10%                     |
| Input Current ( $I_{DD}$ )                             |                              |
| 0.012 ~ 0.040MHz                                       | 3 mA                         |
| >0.040 ~ 1.500MHz                                      | 6 mA                         |
| >1.500 ~ 32.000MHz                                     | 15 mA                        |
| >32.000 ~ 50.000MHz                                    | 20 mA                        |
| >50.000 ~ 67.000MHz                                    | 25 mA                        |
| >67.000 ~ 170.000MHz                                   | 40 mA                        |
| Standby Current                                        | 10 $\mu$ A                   |
| Output Symmetry (50% $V_{DD}$ )                        |                              |
| 0.012 ~ 50.000MHz                                      | 45% ~ 55%                    |
| >50.000 ~ 170.000MHz                                   | 40% ~ 60%                    |
| Rise/Fall Time (10%/90% $V_{DD}$ Levels) ( $T_R/T_F$ ) |                              |
| 0.012 ~ 80.000MHz                                      | 6 nS                         |
| >80.000 ~ 125.000MHz                                   | 4 nS                         |
| >125.000 ~ 170.000MHz                                  | 3 nS                         |
| Output Voltage ( $V_{OL}$ )                            | 10% $V_{DD}$                 |
| ( $V_{OH}$ )                                           | 90% $V_{DD}$ Min             |
| Output Load (HCMOS)                                    | 15pF                         |
| Start-up Time ( $T_S$ )                                | 10 mS                        |
| Output Disable Time 1                                  | 150 nS                       |
| Output Enable Time 1                                   | 10 mS                        |


| ENABLE / DISABLE FUNCTION          |                |
|------------------------------------|----------------|
| Pin <sup>1</sup>                   | Output (pin 3) |
| OPEN <sup>1</sup>                  | Active         |
| '1' Level $V_{IH} \geq 70\%V_{DD}$ | Active         |
| '0' Level $V_{IL} \leq 30\%V_{DD}$ | High Z         |

| Available Options by Stability & Operating Temp for 3.3V |                            |                       |
|----------------------------------------------------------|----------------------------|-----------------------|
| Frequency Stability                                      | Operating Temperature (°C) | Frequency Range (MHz) |
| ±100PPM <sup>2</sup>                                     | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±100PPM <sup>2</sup>                                     | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±100PPM <sup>2</sup>                                     | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±50PPM <sup>2</sup>                                      | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±25PPM <sup>2</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±25PPM <sup>2</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |
| ±25PPM <sup>3</sup>                                      | -40 ~ +85                  | 0.012 ~ 170.000       |
| ±20PPM <sup>3</sup>                                      | -10 ~ +70                  | 0.012 ~ 170.000       |
| ±20PPM <sup>3</sup>                                      | -20 ~ +70                  | 0.012 ~ 170.000       |

<sup>1</sup> An internal pull-up resistor from pin 1 to pin 4 allows active output if pin 1 is left open

<sup>2</sup> Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, Reflow, and one-year aging.

<sup>3</sup> Inclusive of 25°C tolerance and operating temperature rang.



| STANDARD SPECIFICATIONS                        |                                    |
|------------------------------------------------|------------------------------------|
| PARAMETERS                                     | MAX (Unless otherwise noted)       |
| Maximum Soldering Temp / Time                  | 260°C / 10 Seconds x 2             |
| Moisture Sensitivity Level (MSL) per J-STD-033 | N/A                                |
| Termination Finish                             | Au (0.3~1μm) over Ni (1.27~8.89μm) |
| Seal Method                                    | Seam                               |
| Lead (Pb) Free                                 | Yes                                |
| RoHS Compliant                                 | Yes, no exemptions                 |
| RERACH Compliant (latest version)              | Yes                                |


# FO7HS

(Former F4500, F4400, F4100 Series)

7mm x 5mm  
HCMOS SMD Oscillator



| TAPE SPECIFICATIONS (mm) |     |     |     |      |      |             | REEL SPECIFICATIONS (mm) |     |     |     |      |      |     |
|--------------------------|-----|-----|-----|------|------|-------------|--------------------------|-----|-----|-----|------|------|-----|
| A                        | B   | C   | D   | E    | F    | REEL QTY    | G                        | H   | I   | J   | K    | L    | M   |
| ø1.5                     | 4.0 | 8.0 | 7.5 | 16.0 | 2.15 | -T1 = 1,000 | 2.0                      | ø13 | ø21 | ø80 | ø255 | 17.5 | 2.0 |



\* Not all frequencies in the frequency range, or every combination of stability, temp range, and voltage available.  
See stabilities and op temps for each V<sub>DD</sub>.

| Available Options & Part Identification for HCMOS SMD Oscillator FO7HS* |                     |                                                                                    |                                                                                  |                                                                                                 |                        |                                                               |
|-------------------------------------------------------------------------|---------------------|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|------------------------|---------------------------------------------------------------|
| Sample PN: <u>FO7HSCBM25.0-T1</u>                                       |                     |                                                                                    |                                                                                  |                                                                                                 |                        |                                                               |
| F                                                                       | O7HS                | C                                                                                  | B                                                                                | M                                                                                               | 25.0                   | -T1                                                           |
| <u>Fox</u>                                                              | <u>Model Number</u> | <u>Voltage</u><br>B = 3.3V±5%<br><b>C = 3.3V±10%</b><br>H = 2.5V±5%<br>K = 1.8V±5% | <u>Stability</u><br>A = ±100PPM<br><b>B = ±50PPM</b><br>D = ±25PPM<br>E = ±20PPM | <u>Operating Temperature</u><br>E = -10 to +70°C<br>F = -20 to +70°C<br><b>M = -40 to +85°C</b> | <u>Frequency (MHz)</u> | <u>Values Added Options</u><br>Blank = Bulk<br>T1 = 1,000 pcs |

| Reliability Test Conditions                         |
|-----------------------------------------------------|
| Please contact Abracon Quality Assurance department |