






Poles	02	03	04	05	06	07	08	09	10	11	12	
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	
TOL	±0.15				±0.25				±0.30			

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.08.08	The Solid wire, Operating temperature and Stranded wire are changed	Jacke
△	2009.08.08	Add UL standard	Jacke
△	2009.08.08	Add the tolerance table	Jacke
△	2010.02.07	The workmanship is changed.	Jacke
△	2010.03.29	The design is changed	Jacke
△	2010.04.16	The dimension is changed	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating "--" slot type
- △ ● Item c Female contact: PhBz (CuSn) Tin plated (Plating before stamping)
- Item d Terminal (housing) : Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- △ ● Solid wire(AWG): 12-26
- △ ● Stranded wire(AWG): 12-26
- Torque: 3.5Lb-In
- Screw: M3.0
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- △ ● Safety Approval: us
- Use with OP Ø1.3mm pin, Withdrawal force: 200 - 500gf /pole


TX xx 01x0 xxxx G

02 2 CONTACTS	0 Black (RAL9005)	RoHS Pb<40,000ppm 000 0 Standard @ Logo 000 A Standard ANY Logo Any special item by customer request, please contact sales department.
03 3 CONTACTS	2 Red (RAL3001/D)	
... ..	3 Orange(RAL2011/P)	
12 12 CONTACTS	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TX-5.0mm Series "--" Solid Block Type				
PART NO.	TXxx01x0xxxxG			DWG NO.	8TX0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Jacke 2010.04.19	Jacke 2010.02.07			X. ±0.50
						X.X ±0.30
						X.XX ±0.10
SHEET: 01/01				UNIT: mm	X° ±1°	
				SCALE: NONE		
				REV.: G		