







DIMENSION

Dim A	NX5.00+1.40
Dim B	(N-1)X5.00

N=Number of contacts

Poles	Tolerance
1p-6p	±0.10
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	04/05'13	change the structure & update the drawing	Da cheng
△	10/17'13	Add is cULus	Da cheng
△			
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Spring clamp: Stainless steel
- Item 3 Solder pin : Brass ,Tin plated
- Item 4 Terminal cover : Thermoplastic (UL 94V-0)

- △ Electrical: cULus
- Voltage rating: 300 V
- Current rating(Sol): 13A
- Current rating(Str): 16 A
- Wire range:
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 12-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval: 
- Critical dimension: 

NJ xx 01 x 0 xxxx G

No. of poles
01 1 CONTACTS
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

△ Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

△ RoHs compliant
(lead<4%)
In copper Alloy
0000:"@ "Logo (Standard)
000A:"ANYTEK "Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NJ- 5.0 Series 1P-24P Horizontal (180D wire inlet)						
PART NO.		NJxx01x0xxxxG			DWG NO.		8NJ0101	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Dacheng 2013.10.21	Dacheng 2013.10.21			UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
							REV.: D	X.XX ±0.10
					SHEET: 01/01		X° ±1°	