


Actuator

704.403.01



<https://eao.com/p/704.403.01>

Your product:



704.403.01 Actuator

FRONT

Front dimension:	Ø 29 mm
Front bezel colour:	Nature
Front bezel material:	Aluminium

MOUNTING

Design:	raised
---------	--------

OPERATING-/INDICATION PART

Lever material:	plastic
Lever colour:	Black
Lever shape:	short

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Mechanical lifetime:	≤2.5 Mio. cycles of operation
Weight:	0.034 kg
Switching angle:	42° left / 42° right
Switching action:	Maintained - Rest - Maintained
Switching positions:	3 positions

AMBIENT CONDITION

Operating temperature: – 40 °C ... + 55 °C

Storage temperature: – 40 °C ... + 85 °C

IP Protection: IP65 front side


OTHER

Short Description: Actuator, Ø 29 mm, optional illuminative, Black, short, Nature, Aluminium, anodised, Maintained - Rest - Maintained

max. number of switching elements: 3


Hints: Max. 3 switching elements can be clipped on

Mounting cut-outs:




A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm

Dimension drawings:



A = Screw terminal

Wiring diagrams:



Switching positions:

