







P.C.B LAYOUT (Top View)

DIM		TOL				
		2P-5P	6P-10P	11P-16P	17P-24P	25P-30P
Dim A	(N-1)×7.62+9.12	±0.20	±0.25	±0.35	±0.40	±0.50
Dim B	(N-1)×7.62	±0.20	±0.25	±0.35	±0.40	±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	2/06'06	Part No. changed	Tony
△	11/20'12	Change the screw plating specification	Jacky
△	11/20'12	Change the electrical specification	Jacky
△	11/20'12	Change the dimensional tolerance	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 250 V, 15 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
△ OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 5.3 Lb-In.
WIRE RANGE: 22 - 16 AWG
1) MOLDED PARTS: THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
△ 3) TERMINAL SCREWS: STEEL, M3
APPROVAL:
△ PART NO.:
Critical dimension:
YK 312 xx 0 x x 00G
G:RoHS compliant(lead<4%) in copper alloy
MARK
0: "@" MARK
1: "ANY" MARK
NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES
TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
△ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE		YK-312 W/O Flange Series			
PART NO.		YK312xx0xx00G		DWG NO.	8YK0001-312
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacky 2012.11.20	Jacky 2012.11.20		
SHEET: 01/01				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				REV.: D	X.XX ±0.10
					X° ±1°