







DIMENSION

Dim A	$N \times 3.81 + 2$
Dim B	$(N-1) \times 3.81$
Dim C	$(N-1) \times 3.81 + 3.9$

N= NUMBER OF POLES

Poles	Dim A	Dim B	Dim C
2P-5P	± 0.15	$+0.15$ -0.0	
6P-10P	± 0.20	$+0.20$ -0.0	
11P-15P	± 0.25	$+0.25$ -0.0	
16P-20P	± 0.30	$+0.30$ -0.0	
21P-24P	± 0.35	$+0.35$ -0.0	

SIGN	DATE	DESCRIPTION	APPROVER
△	1/27'07	Soldering temperature changed from 245° to 250°	Tony
△	10/10`13	Update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item (a) Contact pin: Copper, Tin plated
- Item (b) Terminal(housing): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C $\pm$ 5°C/5 Sec
- Safety Approval:
- Critical dimension: ▽

VE xx 3 1 x 1 xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

G RoHS compliant
(lead<4%)
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VE-3.81 Series 90° (Close)				
PART NO.	VExx31x1xxxxG			DWG NO.	8VE0004
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 10/10`13	Chen Bo 10/10`13		Tolerance X. ± 0.50 X.X ± 0.30 X.XX ± 0.10 X° $\pm 1^\circ$
					UNIT: mm SCALE: NONE SHEET: 01/01 REV.: E