

SIGN	DATE	DESCRIPTION	APPROVER
△	3/11'09	Dim.A & Dim.B Changed	Tony
△	2009.12.18	Add UL standard	Jacke
△	2010.03.23	Add the 2p mark	Jacke





THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ㉑ Clamp: Steel Zinc plated
- Item ㉒ Terminal(Up body): Thermoplastic (UL94V-0)
- Item ㉓ Terminal(Down body): Thermoplastic (UL94V-0)
- Item ㉔ Female contact: PhBz(CuSn),Tin plated.
- Item ㉕ Terminal screw: Steel Zinc plating "- " slot type
- Item ㉖ Clampage:Steel/steel Zinc plated
- Electrical: cULus
- Voltage rating: 300V
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5 Lb-In.
- Screw: M2.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Safety Approval: cULus

VM xx 0 5 x 1 xxxx G

POLES			G: Pb<40000ppm
02: 02 pole			
... ..			
16: 16 pole			
	Color		0000: "@" Logo (Standard)
	0 Black (RAL9005)		(Steel screw plating Cr ³)
	2 Red (RAL3001/D)		000A: "ANYTEK" Mark
	3 Orange(RAL2011/P)		Any special item by
	4 Yellow(RAL1018/A)		customer request.
	5 Green(RAL6018/T)		please contact sales
	6 Blue (RAL5015/A)		department.
	8 Grey(RAL7035/D)		



POLE		2	3	4	5	6	7	8
A		13.24	20.86	28.48	36.10	43.72	51.34	58.96
B		7.62	15.24	22.86	30.48	38.10	45.72	53.34
Tol.		±0.15			±0.20			
POLE	9	10	11	12	13	14	15	16
A	66.58	74.20	81.82	89.44	97.06	104.68	112.30	119.92
B	60.96	68.58	76.20	83.82	91.44	99.06	106.68	114.30
Tol.		±0.30			±0.40			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VM 7.62 mm W/O Flange Series						
PART NO.	VMxx05x1xxxxG			DWG NO.	8VM0502		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Jacke 2010.03.23	Jacke 2009.12.18		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
				SHEET: 01/01	REV.: E	X°	±1°