



1	2	3	4	5	6	7
---	---	---	---	---	---	---

SIGN	DATE	DESCRIPTION	APPROVER
⚠	01/20/07	The Soldering temperature from 245° to 250°	Aaron
⚠	2010.08.12	The design is changed	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



N=Number of contacts



P.C.B. LAYOUT

2-6p	± 0.20	± 0.20
6-12p	± 0.25	± 0.25
12-24p	± 0.40	± 0.40

Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Pull force:
- Screw:
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:  

HA xx 31 x 0 xxxx G	G: Pb<40,000ppm
02 2 CONTACTS	2 Red
03 3 CONTACTS	3 Orange
...	5 Green(RAL6018/T)
24 24 CONTACTS	8 Grey(RAL7004/P)
	Any special item by customer request, please contact sales department.

ANYTEK			CUSTOMER COPY		
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD					
TITLE	HA-5.0mm 180°				
PART NO.	HAxx31x0xxxxG			DWG NO.	8HA0008
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
				Chen Bo 2010.08.12	X: ± 0.50 X.X: ± 0.30 X.XX: ± 0.10 X°: $\pm 1°$
					UNIT: mm SCALE: NONE
				SHEET: 01/01	REV.: F