

Actuator

704.407.018I



<https://eao.com/p/704.407.018I>

Your product:



704.407.018I Actuator

FRONT

Front bezel colour:	Nature
Front dimension:	Ø 35 mm
Front bezel material:	Aluminium

MOUNTING

Design:	flush
Mounting cut-out:	Ø 30.5 mm

OPERATING-/INDICATION PART

Lever shape:	short
Lever colour:	Black
Lever material:	plastic

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
------------	---

MECHANICAL CHARACTERISTIC

Switching positions:	3 positions
Mechanical lifetime:	≤2.5 Mio. cycles of operation
Switching angle:	42° left / 42° right
Weight:	0.056 kg
Switching action:	Maintained - Rest - Momentary


AMBIENT CONDITION

Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C
IP Protection:	IP65 front side

OTHER


max. number of switching elements:	3
Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, optional illuminative, Black, short, Nature, Aluminium, anodised, Maintained - Rest - Momentary
Hints:	Max. 3 switching elements can be clipped on

Dimension drawings:




X = Screw terminal


Wiring diagrams:



Switching positions:



Mounting cut-outs:



- A = Screw terminal
- B = Push-in terminal (PIT)
- C = Plug-in terminal 6.3 mm x 0.8 mm
- D = Double plug-in terminal 6.3 mm x 0.8 mm