








SIGN	DATE	DESCRIPTION	APPROVER
△	1/31/07	The soldering temperature from 245° to 250°	Aaron
△	05/28'13	change the structure	Da cheng
△	05/28'13	update the drawing	Da cheng
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover :Thermoplastic (UL94V-0)
- Item ③ Contact pin : Brass,Tin plated
- Item ④ Wire guard: Stainless steel
- Item ⑤ Pad board: Thermoplastic (UL94V-0)


Electrical:

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 16KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension:



△ N=NUMBER OF POLES

Dim L	(N-1)×7.62+6.58
Dim B	(N-1)×7.62



POLES	Dim L	Dim B
1p	±0.15	
2p-4p	±0.2	±0.15
5p-8p	±0.3	±0.25
9p-12p	±0.4	±0.35
13p-16p	±0.45	±0.4

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE				HM 7.62 mm Series press fit type			
PART NO.				DWG NO.			
HMxx40x1xxxxG				8HM0104			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.	
Da cheng		2013.05.28	2013.05.28	Da cheng		2013.05.28	
SHEET: 01/01				REV.: D			
UNIT: mm				Tolerance			
SCALE: NONE				X, ±0.50			
X, ±0.30				X, ±0.10			
X°, ±1°							