





DIMENSION

Dim.L	$(N/2-1) \times 3.81 + 14.8$
Dim.P	$(N/2-1) \times 3.81$
Dim.A	$(N/2-1) \times 3.81$

N = Number of poles

	TOL		
	2×2P-2×5P	2×6P-2×16P	2×17P-2×24P
Dim.L	±0.20	±0.30	±0.40
Dim.P	±0.15	±0.25	±0.30
Dim.A	±0.15	±0.25	±0.30

SECTION Q-Q

SIGN	DATE	DESCRIPTION	APPROVER
△	9/17'10	How to older is changed	Runner
△	05/27'11	Voltage rating is changed from 160 V to 300 V	Steven
△	05/27'11	Withstanding Voltage is changed from 1.32 Kv to 1.6 Kv	Steven
△	05/27'11	Add "cULus" Safety Approval logo	Steven
△	04/16'12	Flange nut is changed	Runner
△	04/16'12	The dimension is added	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: PA66 30% GF (UL94V-0)
- Item ② Contact pin : Copper Tin plated
- Item ③ With flange nut: Brass M2.5

Electrical:

- Voltage rating: 300V
- Current rating: 5.5A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec
- Safety Approval: cULus
- Critical dimension:

KE xx 3 2 x 0 xxxx G

No. OF POLES

04: 2×2 POLES

06: 2×3 POLES

...

48: 2×24 POLES

COLOR

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

RoHS compliant (lead<4%)

In copper Alloy

A00 0: "@" Mark

A00 A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KE 3.81mm With Flange Series (Vertical) DIP type						
PART NO.	KExx32x0xxxxG			DWG NO.	8KE0312		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Runner 2012.04.16	Runner 2010.04.12		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: E	X.XX ±0.10	
						X° ±1°	