

SUMMARY

Wires

Low voltage 19



Image is for illustrative purpose only

Series 2P
Termination type Male solder
IP rating 66
AWG wire size 30.00 - 22.00
Cable Ø 3.20 - 5.20 mm
Status active
Matching parts [CNB.M19.GLLR](#)

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model CF*: Straight plug with cable collet, watertight (IP 66) and nut for fitting a bend relief
Keying 3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material PSU (Polysulfone), gray
Weight 9.62 g

Performance

Configuration 2P.M19 : 19 Low V.
Insulator L: PEEK for solder contacts
Rated Current 5 Amps

Specifications


Contact Type: Solder
Contact Dia.: 0.7 mm (0.027in)
Bucket Dia.: 0.8 mm (0.031in)
Test voltage (kV rms) Contact-contact: 1.4
Air clearance min.: 0.6 mm
Creepage distance min.: 0.6 mm

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): >1000 mating cycles
Temp (min / max): -50°C / +150°C
F ret (min): 150 N
F ret (max): 250 N
Steam sterilization: 20 times (with potting on rear connection)

DRAWINGS



RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.