






SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




Material:

- Item a :Male contact pin: Copper Tin plated
- Item b :Terminal(housing): Thermoplastic (UL94V-0)
- Electrical: cULus
- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus



SECTION A-A



N = Number of poles
 Dim A=Nx5.0+3.2
 Dim B=Nx5.0+0.7
 Dim C=(N-1)x5.0

	Dim A	Dim B	Dim C
2-6p	±0.20	^{+0.15} ₋₀	±0.20
6-12p	±0.30	^{+0.3} ₋₀	±0.30
12-24p	±0.40	^{+0.4} ₋₀	±0.40

NC xx 7 2 x 0 xxxx G

02 2 poles
 03 3 poles
 ...
 24 24 poles

0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange(RAL2011/P)
 4 Yellow(RAL1018/A)
 5 Green(RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)

G: Pb<40,000ppm

any special item by
 customer request,
 please contact sales
 department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NC 5.0mm Vertical W/hook holder (100% protected against mismatching)						
PART NO.	NCxx72x0xxxxG			DWG NO.	8NC0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Runner 2010.08.11	Runner 2010.08.11		UNIT: mm		X. ±0.50
					SCALE: 2/1		X.X ±0.30
					SHEET: 01/01 REV.: B		X.XX ±0.10 X° ±1°