

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION





ALL RIGHTS RESERVED

© COPYRIGHT


By

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APR
	G3	REVISED PER ECO-14-013067	27AUG2014	NK	M.
	H	REVISED PER ECO-17-004657	05APR2017	RS	M.




RECOMMENDED P.C. BOARD LAYOUT



RECOMMENDED PANEL CUTOUT

- | | |
|---|---|
| 1 | CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE. |
| 2 | NYLON, UL 94V-0 RATED, BLACK. |
| 3 | CONTACT BODY: 0.76um[.000030] MIN GOLD FOR LENGTH OF 5.08[.200] MIN FROM MATING END,
WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL.
CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER. |
| 4 | CONTACT BODY: 2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.
CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER. |
| 5 | CONTACT BODY: 0.76um[.000030] MIN GOLD FOR LENGTH OF 5.08[.200] MIN FROM MATING END,
WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL.
CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER. |
| 6 | CONTACT BODY: 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL.
CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER. |
| 7 | PRELIMINARY PART NUMBER. |
| 8 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

△ OBSOLETE	11.35[.447]	4-40 UNC, INSERT, BRASS	△ ₅	1-213729-1
	14.22[.560]	4-40 UNC, INSERT, BRASS	△ ₅	1-213729-0
△ OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	△ ₅	213729-9
	4.04[.159]	4-40UNC, INSERT, BRASS	△ ₆	213729-8
△ OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	△ ₆	213729-7
	9.35[.368]	4-40UNC, INSERT, BRASS	△ ₅	213729-6
△ OBSOLETE	4.04[.159]	3.81±0.08[.150±.003] DIA	△ ₄	213729-5
△ OBSOLETE	4.04[.159]	4-40UNC, INSERT, BRASS	△ ₄	213729-4
△ OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	△ ₄	213729-3
	9.35[.368]	4-40UNC, INSERT, BRASS	△ ₃	213729-2
△ OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	△ ₃	213729-1
	C	A	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN W.G. LENKER 12-3-91		 TE Connectivity			
		CHK R. STONE 12-11-91					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC	±	PRODUCT SPEC	RECEPTACLE ASSEMBLY, POSTED, SERIES 1, REVERSE SEX, CPC			
	1 PLC	±	108-10024				
	2 PLC	± 0.25 [0.10]	APPLICATION SPEC				
	3 PLC	±	114-10004				
	4 PLC	±					
ANGLES:		±		SIZE	CAGE CODE	DRAWING NO	RESTRICTED
MATERIAL		FINISH	WEIGHT	A1	00779	C=213729	—
RECEPTACLE: 		—		SCALE		SHEET	REV
CONTACT: BRASS			CUSTOMER DRAWING	2:1	1 of 1		