







PCB LAYOUT
Bottom view



Dimension

DIM A	$(N-1) \times 10.16 + 5.98$
DIM B	$(N-1) \times 10.16$

N=Number of poles

POLES	DIM B	DIM A
2p-4p	± 0.15	± 0.20
5p-7p	± 0.20	± 0.25
8p-10p	± 0.25	± 0.30
11p-12p	± 0.30	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/27'07	The soldering temperature from 245°to 250°	Aaron
△	10/09'12	Update the drawing	Da cheng
△	04/19'13	Update the drawing	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Terminal body (Contact pin): Brass,Tin plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: △

HG xx 40 x 0 xxxx G

02 2 CONTACTS	Color △△	000 0 Standard @ Logo	RoHS compliant
03 3 CONTACTS	0 Black (RAL9005)	000 A Standard ANY Logo (lead<4%)	△
...	2 Red (RAL3001/D)	Any special item by	In copper Alloy
12 12 CONTACTS	3 Orange(RAL2011/P)	customer request,	
	4 Yellow(RAL1018/A)	please contact sales	
	5 Green(RAL6018/T)	department.	
	6 Blue (RAL5015/A)		
	8 Grey(RAL7004/P)		
	9 White(RAL1102)		
	C Multiple colors		

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE	HG 10.16mm Series				
PART NO.	HGxx40x0xxxxG			DWG NO.	8HG0501
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacky 2013.04.19	Jacky 2013.04.19		
					Tolerance
				SHEET: 01/01	X. ±0.50
				UNIT: mm	X.X ±0.30
				SCALE: NONE	X.XX ±0.10
				REV.: F	X° ±1°