



Description: 2mm Single Row Receptacle
--





Material:


Insulator: Nylon-6T, Black, UL 94V-O
Process Temperature: 260°C for 10 seconds
Contact: Phosphor Bronze

Electrical:

Current Rating: 2 Amps
Contact Resistance: 20 mOhms Max.
Insulation Resistance: 5000 MOhms Min.
Working Voltage: 250V
Temperature: -40° C TO +105° C



Recommended P.C. Board Hole Layout



Units = mm

Tolerance
.X ± 0.3
.XX ± 0.20
.XXX ± 0.100

Series

2563 = Single Row

Position

Single - Increments of 1
(02 to 40)

Type

01 = Straight

Plating Options

P2 = Gold Flash



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

3	DRAWN:
0	PAM JENKINS

DATE:	1-30-06
-------	---------

NorComp

SCALE:	NTS
--------	-----

SHEET	OF
1	1

REV
3

DWG NO. 2563YY01RP2