





N=Number of poles

Dim L = $(N/2 - 1) \times 3.5 + 4.0$
Dim P = $(N/2 - 1) \times 3.5$
Dim C = $N/2 \times 3.5 - 0.6$
Dim D = $(N/2 - 1) \times 3.5 + 10.3$
Dim E = $(N/2 - 1) \times 3.5 + 7.0$

POLES \ Dim.	Dim.L	Dim.P	Dim.C	Dim.D	Dim.E
Tol					
2x2p-2x6p	±0.15	±0.10	$\begin{smallmatrix} +0.0 \\ -0.15 \end{smallmatrix}$	±0.10	±0.15
2x7p-2x12p	±0.25	±0.20	$\begin{smallmatrix} +0.0 \\ -0.20 \end{smallmatrix}$	±0.20	±0.25
2x13p-2x18p	±0.30	±0.25	$\begin{smallmatrix} +0.0 \\ -0.25 \end{smallmatrix}$	±0.25	±0.30
2x19p-2x24p	±0.40	±0.35	$\begin{smallmatrix} +0.0 \\ -0.30 \end{smallmatrix}$	±0.35	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	05/24`11	The cULus is added	Runner
△	05/24`11	The dimension is added	Runner
THIS IS CAD DRAWING. DO NOT REVISE MANUALLY!!!			

Material

- Item④ Terminal up housing Thermoplastic (UL94V-0)
- Item⑤ Terminal down housing Thermoplastic (UL94V-0)
- Item⑥ Spring clamp Stainless steel
- Item⑦ Female contact PbZn , Tin plated
- Item⑧ With flange screw steel M2.0 Zinc plated “-” slot type

Electrical

cULus

- Voltage rating: 150V
- Current rating: 7A
- Solid wire(AWG): 18-28
- Stranded wire(AWG): 18-28
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40℃ to +115℃
- Safety Approval: 
- Critical dimension: 

V W x x 1 0 x 1 x x x x G

NO of poles

04 2x2 CONTACTS

06 3x2 CONTACTS

48 24x2 CONTACT

0 Black

3 Orange

5 Green

6 Blue

8 Grey

➤ RoHS
Pb<40,000ppm

0000 Standard @ Logo

000A Standard ANY Logo

Any special item by customer request, please contact sales department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VW 3.5mm Series With flange					
PART NO.		VWxx10x1xxxxG		DWG NO.		8VW0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Runner 2011.05.25	Chen Bo 2011.05.25			X. ±0.50
							UNIT: mm
					SCALE: NONE		X.XX ±0.10
					REV: C		X° ±1°
					SHEET: 01/01		