


SIGN	DATE	DESCRIPTION	APPROVER
	2009.03.31	Add the inspection dimension	Jacke
	2010.05.30	Add cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item④Clamp: Brass(CuZn) Ni plated
- Item⑤Terminal screw: Steel Zinc plating "-" slot type
- Item⑥Female contact: PbZn (CuSn) Tin plated
- Item⑦Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300V
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 14-26
 - Stranded wire(AWG): 14-26
 - Torque: 3.5Lb-In
 - Screw: M2.6
 - Wire strip length: 5-6mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature:-40°C to +115°C
- ▲ ● Safety Approval: 

KR xx 01 x 1 xxxx G

Pb<40,000ppm

Poles	0	Black (RAL9005)	0000 Standard @ Logo
02 2Contacts	2	Red (RAL3001/D)	000A Standard ANY Logo
03 3Contacts	3	Orange(RAL2011/P)	Any special item by
— ———	4	Yellow(RAL1018/A)	customer request,
24 24Contacts	5	Green(RAL6018/T)	please contact sales
	6	Blue (RAL5015/A)	department.
	8	Grey(RAL7035/D)	

N = Number of poles

Dim A=Nx5.0

$$\text{Dim } B = (N-1) \times 5.0$$

Dim B=(N-1)x5.0				
	Dim A	Dim B	Dim C	Dim D
2P	±0.05	±0.05	≤0.05	≤0.05
3-6p	±0.15	±0.15	≤0.10	≤0.10
7-12p	±0.20	±0.20	≤0.20	≤0.20
13-18p	±0.30	±0.30		
19-24p	±0.40	±0.40		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KR 5.0mm Series "- "(With hook)						
PART NO.	KRxx01x1xxxxG			DWG NO.	8KR0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2010.05.30	Jacke 2009.03.31			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: D	X.XX ±0.10
							X° ±1°