





SIGN	DATE	DESCRIPTION	APPROVER
△	08/13'12	structure design is changed	Dacheng
△	08/25'12	Changed from 250°C±10°/5 Sec to 260°C±5°C/5 Sec	Dacheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



- Material:**
- Item ① Terminal lever: Thermoplastic (UL94V-0)
 - Item ② Terminal housing: Thermoplastic (UL94V-0)
 - Item ③ Spring clamp: Stainless steel
 - Item ④ Solder pin: Brass. Tin plated
 - Item ⑤ Terminal cover: Thermoplastic (UL94V-0)
 - Item ⑥ Terminal pad board : Thermoplastic (UL94V-0)

- Electrical:**
- | | | |
|----------------------------|------------------|----------------------|
| | cULus | VDE |
| ● Voltage rating: | 300 V | 450 V |
| ● Current rating: | 11 A | 12 A |
| ● Wire range: | | 0.5-4mm ² |
| ● Solid wire(AWG): | 12-20 | |
| ● Stranded wire(AWG): | 12-20 | |
| ● Wire strip length: | 10-11 mm | |
| ● Withstanding Voltage: | 1.6KV | 2.5KV |
| ● Operating temperature: | -40°C to +115°C | |
| △ ● Soldering temperature: | 260°C ±5°C/5 Sec | |
| ● Safety Approval: | | |
| ● Critical dimension: | ▽ | △ VDE |



H6 xx 1 0 x 0 xxxx G

No. OF POLES: 02: 2 POLES, : , 16: 16 POLES

COLOR: 0: BLACK, 5: GREEN (RAL 6018/T), 6: BLUE, 8: GREY (RAL 7004/P)

G: RoHs compliant (lead<4%) In copper Alloy


1000: "@ " Logo (Standard)

100A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

N = Number of poles
 Dim L=N x7.5-1.0
 Dim P=(N-1)x7.5

	Dim L	Dim P
2-6p	±0.15	
7-12p	±0.25	
13-16p	±0.40	



PCB Layout

ANYTEK				CUSTOMER COPY	
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO.,LTD					
TITLE	H6 7.5mm Series (Square hloe)				
PART NO.	H6xx10x0xxxxG		DWG NO.	8H60501	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Dacheng 2012.08.25	Dacheng 2012.08.25		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
				UNIT: mm SCALE: NONE REV.: D	
				SHEET: 01/01	